

## 75 Ohm N Male to 75 Ohm N Male Cable 75 Ohm Armored Test Coax in 60 cm with LF Solder

The 75 ohm type N male to 75 ohm type N male 60 cm cable using 75 ohm armored test coax, part number FMCA1032-60CM, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 75 ohm flexible flexible cable coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1032-60CM type N male to type N male cable assembly operates to 3 GHz. FMCA1032-60CM is a general purpose 75 Ohm Flexible Armored Test Cable exhibits excellent insertion loss and return loss values with operation up to 3 GHz. These test cables are suitable for engineering labs, production environments and quality testing facilities. The FMCA1032-60CM test cable is a good choice for use with 75 Ohm S-parameter test systems and these cables meet ANSI/SCTE 99 2009 pull force and ANSI/SCTE 98 2009 tightening torque standards.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.16:1	
Inductance		75 [246.06]		uH/ft [uH/m]
Dielectric Withstanding Voltage (AC)			700	Vrms

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	3			GHz
Insertion Loss (Typ.)	0.22	0.328	0.386			dB
VSWR (Max.)	1.04:1	1.07:1	1.08:1			
Return Loss (Max.)	35	30	28			dB

### Mechanical Specifications

#### Cable Assembly

Length*	23.622 in [600 mm]
Weight	0.4075 lbs [184.84 g]

#### Cable

Cable Type	Flexible Cable
Impedance	75 Ohms
Inner Conductor Type	Bare Copper
Inner Conductor Material and Plating	Copper
Dielectric Type	Polyethylene
Shield Layer 1	Copper
Jacket Material	PVC, Black
Jacket Diameter	0.3 in [7.62 mm]



### Configuration:

- N Male
- N Male
- Flexible Cable

### Features:

- Max Frequency 3 GHz
- PVC Jacket
- DC-3GHz
- Low Insertion loss
- Excellent Return loss Greater than 28 dB
- ANSI/SCTE 99 2009 pull force
- Rugged Protective Outer Jacket
- Specially designed for Testing of 75 Ohm communication systems.
- Custom lengths available upon request.

### Applications:

- General Purpose
- Laboratory Use
- Test & Measurement
- Lab Equipment Accessories
- General Purpose Test and Evaluation
- Engineering Prototype Evaluation

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Typical Flex Cycles 100,000  
Tensile Strength 40 lbs [18.14 Kg]

**Connectors**

Description	Connector 1	Connector 2
Type	N Male	N Male
Impedance	75 Ohms	75 Ohms
Contact Material & Plating	Copper, Gold	Copper, Gold
Dielectric Type	PE	PE

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**FMCA1032 - xx uu**

cm = Centimeters  
<blank> = Inches  
Length


Example: FMCA1032-12 = 12 inches long cable  
FMCA1032-100cm = 100 cm long cable

75 Ohm N Male to 75 Ohm N Male Cable 75 Ohm Armored Test Coax in 60 cm with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [75 Ohm N Male to 75 Ohm N Male Cable 75 Ohm Armored Test Coax in 60 cm with LF Solder FMCA1032-60CM](#)

URL: <https://www.fairviewmicrowave.com/n-male-n-male-cable-flexible-cable-coax-fmca1032-60cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 75 Ohm N Male to 75 Ohm N Male Cable 75 Ohm Armored Test Coax in 60 cm with LF Solder		DWG NO FMCA1032		CAGE CODE 3FKR5	
CAD FILE	031115	SHEET		SCALE	N/A
				SIZE	A 150