

Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components



FMCA100027

Configuration


Connector 1: F MaleConnector 2: F Male

Cable Type: LMR-240-75-DB

· Coax Cable Group: 94

Features

- · Max Frequency 2 GHz
- 84% Phase Velocity
- · PE Jacket



Applications

· General Purpose

· Laboratory Use

Description

The 75 ohm type F male to 75 ohm type F male cable using 75 ohm LMR-240-75-DB coax, part number FMCA100027, from Fairview Microwave is in-stock and ships same day. This Fairview type F to type F cable assembly has a male to male gender configuration with 75 ohm LMR-240-75-DB coax. The FMCA100027 type F male to type F male cable assembly operates to 2 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%

Specifications by Frequency



Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components



FMCA100027

Part Number	Number Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
Part Number		Frequency	50	100	250	500	2000	MHz	weight (ms)
FMCA100027	Custom Lengths	Insertion Loss (Typ.)	0.016	0.022	0.036	0.052	0.109	dB/ft	
TWCA100027	Available	ilisertion Loss (Typ.)	0.06	0.08	0.12	0.18	0.36	dB/m	
FMCA100027-12	12 Inch	Insertion Loss (Typ.)	0.22	0.23	0.24	0.26	0.31	dB	0.067
FMCA100027-24	24 Inch	Insertion Loss (Typ.)	0.24	0.25	0.28	0.31	0.42	dB	0.103
FMCA100027-36	36 Inch	Insertion Loss (Typ.)	0.25	0.27	0.31	0.36	0.53	dB	0.138
FMCA100027-48	48 Inch	Insertion Loss (Typ.)	0.27	0.29	0.35	0.41	0.64	dB	0.173
FMCA100027-60	60 Inch	Insertion Loss (Typ.)	0.28	0.31	0.38	0.46	0.75	dB	0.208

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB Loss due to Connector 2: 0.1 dB Base Weight: 0.067 pounds Additional Weight per Inch: 0.00292 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm] Weight 0.067 lbs [30.39 g]

Cable

Cable Type LMR-240-75-DB Impedance 75 Ohms Inner Conductor Type Stranded Inner Conductor Material and Plating Copper Dielectric Type Foam PE Outer Conductor 1 Material and Plating Aluminum Tape Outer Conductor Diameter 0.155 in [3.94 mm] PΕ

Jacket Material

Jacket Diameter 0.24 in [6.1 mm]

Connectors

Description	Connector 1	Connector 2		
Туре	F Male	F Male		
Impedance	75 Ohms	75 Ohms		
Configuration	Straight	Straight		
Contact Material and Plating	Beryllium Copper	Beryllium Copper		
Dielectric Type	PTFE	PTFE		
Body Material and Plating	Nickel, Gold over Copper	Nickel, Gold over Copper		
Body Plating Specification	50 μin minimum	50 μin minimum		



Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components



FMCA100027

Environmental Specifications

Operating Range Temperature

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data

How to Order



Example: FMCA100027-12 = 12 inches long cable

FMCA100027-100cm = 100 cm long cable

Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components FMCA100027

URL: https://www.fairviewmicrowave.com/low-loss-75-ohm-f-male-to-75-ohm-f-male-cable-75-ohm-lmr-240-75-db-coax-with-times-microwave-components-fmca100027-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA100027 CAD Drawing

Low Loss 75 Ohm F Male to 75 Ohm F Male Cable 75 Ohm LMR-240-75-DB Coax with Times Microwave Components

