



Low PIM N Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax

Low PIM N male to 7/16 DIN male part number FMCA1307 from Fairview Microwave is in-stock and ships same day. This low PIM N male to 7/16 DIN male plenum coax cable assembly offers low PIM performance to support Distributed Antenna Systems (DAS), in-building wireless and other emerging mobile communication networks. The SPP-250-LLPL coax cable carries a UL910 rating for plenum installations. Each low PIM N male to 7/16 DIN male cable assembly is marked with its actual Passive Intermodulation (PIM) test result.

Fairview's FMCA1307 datasheet specifications and outline drawing are shown below in this PDF. Our extensive offering of low PIM cable assemblies, low-PIM adapters and other RF products support multi-carrier system prototype, cable installations and PIM testing applications.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits	
Frequency Range	DC			6		GHz	
VSWR				1.35:1			
Velocity of Propagation		7	76			%	
RF Shielding	100					dB	
Passive Intermodulation		-1	.65	-160		dBc	
Capacitance		26.7	[87.6]		pF/f	t [pF/m	n]
Operating Voltage (AC)				750	١	/rms	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	6	GHz
Insertion Loss (Max.)	0.04	0.05	0.08	0.12	0.15	dB/ft
	0.13	0.16	0.26	0.39	0.49	dB/m
VSWR (Max.)	1.25:1	1.25:1	1.25:1	1.35:1	1.35:1	
Power Handling (Max.)	850	507	460	370	250	W

Electrical Specification Notes: Values at 25°C, sea level

PIM test results vary between cables

Insertion Loss does not include the loss of the connetors. Insertion Loss is estimated as 0.4dB of connector loss.

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm] Weight 0.299 lbs [135.62 g]

Cable

Cable Type Inner Conductor Type Solid Inner Conductor Material and Plating Copper, Bare

SPP-250-LLPL



Configuration:

- N Male
- 7/16 DIN Male
- SPP-250-LLPL

Features:

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- Low PIM < -160 dBc
- IP67 (Mated)
- Low Loss with Excellent VSWR
- PIM Test Results Marked on Each
- UL910 Plenum Rated Cable
- Extremely Flexible and Lightweight

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- DAS
- Mobile Networks
- In-Building Wireless
- Small Cells
- PIM Testing

Cable Diagram:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Dielectric Type PTFE Number of Shields 1

Shield Layer 1 Annular Corrugated Copper Tube

Outer Conductor Diameter 0.25 in [6.35 mm] Jacket Material

FEP

0.28 in [7.11 mm] Jacket Diameter

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Connectors

Description	Connector 1	Connector 2		
Туре	N Male	7/16 DIN Male		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Silver	Brass, Silver		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal		
Seal Gasket Material	Silicone Rubber	Silicone Rubber		

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C Plenum Rating UL910

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA1307 - xx uu cm = Centimeters

dlank> = Inches Length

Example: FMCA1307-12 = 12 inches long cable

FMCA1307-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1.2 Page 2 of 4





Low PIM N Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low PIM N Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax FMCA1307


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/low-pim-n-male-7-16-din-male-cable-spp250llpl-coax-fmca1307-p.aspx

described h	erein. It may	be necessar	y to ma	ke modification	ons to the part	and/or t	he document	ation of the par	t, in order
to implemen	nt improvemen	nts. Fairview	Microw	ave reserves	the right to ma	ke such	changes as r	equired. Unless	otherwise
stated, all s	specifications a	re nominal.	Fairvie	w Microwave	does not make	any rep	resentation	or warranty reg	arding the
					urpose, and Fai	rview Mi	crowave doe	s not assume a	ny liability
arising out	of the use of a	ny part or do	cument	tation.					







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			TME.		
Low PIM N Male to 7/16 DIN Male Plenum Cable SPP-	DWG NO FMCA1307			CAGE CODE 3FKR5		
250-LLPL Coax	CAD FILE 12/05/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361