



# Snap-On MMBX Plug to SMA Female Bulkhead Cable RG316 Coax

Fairview Microwave's MMBX cable assemblies are part of our full line of RF interconnects available for same-day shipping. These MMBX cable assemblies are designed for test applications or connection of your MMBX system components. With a high frequency range up to 3 GHz, this family of MMBX cables can also be used to connect your panels to PCB's with between series options like MMBX-to-SMA, MMBX-to-N or MMBX-to-TNC assemblies. There are hundreds of possible cable assembly configurations to choose from, all available same day.

This MMBX cable assembly datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave not only has many MMBX cable assembly options, but also a wide selection of RF, microwave and millimeter wave cable assemblies which allows RF designers to customize their configurations to whatever is required. Whether the need is to provide an I/O for a board design or simply create a custom cable assembly configuration, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom RF cable assemblies for you and ship same day.

## **Electrical Specifications**

Description	Min	Т	ур	Max	ι	Inits
Frequency Range	DC			3		GHz
VSWR				1.4:1		
Return Loss		-15	5.56			dB
Velocity of Propagation		(	59			%
Jacket Spark				2,000	\	/rms

#### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.11	0.16	0.27	0.38	0.58	dB/ft
	0.36	0.52	0.89	1.25	1.9	dB/m

dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

## **Mechanical Specifications**

## **Cable Assembly**

Diameter 0.312 in [7.92 mm]

#### Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

RG316 50 Ohms Stranded Copper Clad Steel, Silver PTFE 1



# **Configuration:**

- Snap-On MMBX Plug
- SMA Female Bulkhead
- RG316


#### **Features:**

- Max. Operating Frequency of 3 GHz
- Snap-On mating

## **Applications:**

- General Purpose MMBX Test
- PCB Testing
- Low Profile MMBX Cable Jumpers
- PCB-to-Panel Connection

# **Cable Diagram:**



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shield Layer 1 Jacket Material Jacket Diameter Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]

#### **Connectors**

Description	Connector 1			Connector 2	
Туре	MMBX Plug		SMA Fem		ale
Mount Method				Bulkhead	
Specification				MIL-STD-3	348
Impedance	50 Ohn	50 Ohms		50 Ohms	
Connection Method	Snap-C	Snap-On			
Mating Cycles	100				
Contact Material & Plating	Beryllium Copp	Beryllium Copper, Gold		Gold	
Contact Plating Spec.				MIL-G-452	204
Dielectric Type	PTFE				
Outer Cond Material & Plat	ing Brass, G	Brass, Gold			
Body Material & Plating	Brass, G	Brass, Gold		Brass, Nickel	
Body Plating Spec.				QQ-N-290	

Mechanical Specification Notes:

## **Environmental Specifications**

**Temperature** 

Operating Range -55 to +155 deg C

Example: FMCA1417-12 = 12 inches long cable

FMCA1417-100cm = 100 cm long cable

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or  $\pm$  3/8", whichever is greater.





Snap-On MMBX Plug to SMA Female Bulkhead Cable RG316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Snap-On MMBX Plug to SMA Female Bulkhead Cable RG316 Coax FMCA1417

URL: https://www.fairviewmicrowave.com/mmbx-plug-sma-female-cable-rg316u-coax-fmca1417-p.aspx









DWG NO

CAD FILE 062217

FAIRVIEW MICROWAVE INC.

Snap-On MMBX Plug to SMA Female Bulkhead Cable

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

RG316 Coax

FMCA1417

SHEET

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

1 OF 1

CAGE CODE

SIZE A

SCALE N/A

3FKR5

9999