

## Black FAKRA Plug to FAKRA Jack Cable 12 Inch Length Using RG174 Coax

The FAKRA plug to FAKRA jack 12 inch cable using RG174 coax, part number FMCA1352A-12, from Fairview Microwave is in-stock and ships same day. This Fairview FAKRA to FAKRA cable assembly has a plug to jack gender configuration with 50 ohm flexible RG174 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1352A-12 FAKRA plug to FAKRA jack cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description             | Min | Typ           | Max   | Units        |
|-------------------------|-----|---------------|-------|--------------|
| Frequency Range         | DC  |               | 1,000 | MHz          |
| VSWR                    |     |               | 1.4:1 |              |
| Velocity of Propagation |     | 66            |       | %            |
| Capacitance             |     | 30.8 [101.05] |       | pF/ft [pF/m] |

### Performance by Frequency

| Description           | F1    | F2    | F3    | F4    | F5    | Units |
|-----------------------|-------|-------|-------|-------|-------|-------|
| Frequency             | 50    | 100   | 250   | 500   | 1,000 | MHz   |
| Insertion Loss (Typ.) | 0.242 | 0.284 | 0.337 | 0.412 | 0.52  | dB    |

### Mechanical Specifications

#### Cable Assembly

Length\* 12 in [304.8 mm]  
Diameter 0.37 in [9.4 mm]

#### Cable

Cable Type RG174  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper Clad Steel  
Dielectric Type PE (LD)  
Number of Shields 1  
Shield Layer 1 Tinned Copper Braid  
Jacket Material PVC, Black  
Jacket Diameter 0.1 in [2.54 mm]



### Configuration:

- FAKRA Plug
- FAKRA Jack
- RG174

### Features:

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

| Description                   | Connector 1           | Connector 2           |
|-------------------------------|-----------------------|-----------------------|
| Type                          | FAKRA Plug            | FAKRA Jack            |
| Configuration                 | Straight              | Straight              |
| Impedance                     | 50 Ohms               | 50 Ohms               |
| Contact Material & Plating    | Phosphor Bronze, Gold | Phosphor Bronze, Gold |
| Dielectric Type               | Teflon                | Teflon                |
| Outer Cond Material & Plating | Brass, Nickel         | Brass, Nickel         |
| Body Material & Plating       | Plastic, Paint        | Plastic               |

**Environmental Specifications**

**Temperature**

Operating Range -40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

**How to Order**

Part Number Configuration:

**FMCA1352A - xx uu**

cm = Centimeters  
<blank> = Inches

Length


Example: FMCA1352A-12 = 12 inches long cable  
FMCA1352A-100cm = 100 cm long cable

Black FAKRA Plug to FAKRA Jack Cable 12 Inch Length Using RG174 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.



Click the following link to obtain additional part information: [Black FAKRA Plug to FAKRA Jack Cable 12 Inch Length Using RG174 Coax FMCA1352A-12](#)

URL: <https://www.fairviewmicrowave.com/fakra-plug-fakra-jack-cable-rg174-coax-fmca1352a-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

|  |   |                  |   |   |
|--|---|------------------|---|---|
|  <b>Fairview Microwave</b><br>an INFINIT <sup>®</sup> brand | UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS |                  | THIRD-ANGLE PROJECTION<br> |   |
|  | TOLERANCES:   |                  | CABLE LENGTH (L) TOLERANCES:  |   |
| TITLE  | .X = ±.2 [5.08]   | FRACTIONS ± 1/32 | L ≤ 12 [305] = +1 [25] / -0   | THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.<br>SHEET 1 OF 1 |
| Black FAKRA Plug to FAKRA Jack Cable 12 Inch Length Using RG174 Coax   | .XX = ±.02 [.51]  | ANGLES ± 1°      | 12 [305] < L ≤ 60 [1524] = +2 [51] / -0   |   |
|  | .XXX = ±.005 [.13]  |                  | 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0  | SCALE N/A   |
|  |   |                  | 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0   |   |
|  |   |                  | 300 [7620] < L = +5%L / -0  |   |
|  | ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.  |                  |   |   |
| SIZE A   | CAGE CODE 3FKR5   | DRAWN BY K.Dang  | ITEM NO. FMCA1352A  | REV B   |

T-Rev.D