



Snap-On MMBX Plug to Snap-On MMBX Plug Cable RG174 Coax

Fairview Microwave's MMBX cable assemblies are part of our full line of RF interconnects available for same-day shipping. These MMBX cable assemblies are designed for test applications or connection of your MMBX system components. With a high frequency range up to 3 GHz, this family of MMBX cables can also be used to connect your panels to PCB's with between series options like MMBX-to-SMA, MMBX-to-N or MMBX-to-TNC assemblies. There are hundreds of possible cable assembly configurations to choose from, all available same day.

This MMBX cable assembly datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave not only has many MMBX cable assembly options, but also a wide selection of RF, microwave and millimeter wave cable assemblies which allows RF designers to customize their configurations to whatever is required. Whether the need is to provide an I/O for a board design or simply create a custom cable assembly configuration, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom RF cable assemblies for you and ship same day.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			3		GHz
VSWR				1.4:1		
Return Loss		-15.56				dB
Velocity of Propagation		6	66			%
Capacitance	31.1 [102.03]			pF/f	t [pF/m]	

Performance by Frequency

F1	F2	F3	F4	F5	Units
50	100	250	500	1,000	MHz
0.06	0.08	0.14	0.22	0.32	dB/ft
0.2	0.26	0.46	0.72	1.05	dB/m
	50	50 100 0.06 0.08	50 100 250 0.06 0.08 0.14	50 100 250 500 0.06 0.08 0.14 0.22	50 100 250 500 1,000 0.06 0.08 0.14 0.22 0.32

dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.185 in [4.7 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

RG174 50 Ohms Stranded Copper Clad Steel, Silver

PE 1



Configuration:

- Snap-On MMBX Plug
- Snap-On MMBX Plug
- RG174


Features:

- Max. Operating Frequency of 3 GHz
- Snap-On mating
- Low Profile Right Angle Configurations
- SMA Bulkhead, N Bulkhead and TNC Bulkhead Between-Series Configurations

Applications:

- General Purpose MMBX Test
- PCB Testing
- Low Profile MMBX Cable Jumpers
- PCB-to-Panel Connection

Cable Diagram:



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shield Layer 1 Jacket Material Jacket Diameter Tinned Copper Braid PVC, Black 0.11 in [2.79 mm]

Connectors

Description	Connector 1	Connector 2
Туре	MMBX Plug	MMBX Plug
Impedance	50 Ohms	50 Ohms
Connection Method	Snap-On	Snap-On
Mating Cycles	100	100
Contact Material & Plating	Beryllium Copper, G	old Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plati	ng Brass, Gold	Brass, Gold
Body Material & Plating	Brass, Gold	Brass, Gold

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA1431 - xx uu | cm = Centimeters | cblank > = Inches | Length

Example: FMCA1431-12 = 12 inches long cable

FMCA1431-100cm = 100 cm long cable

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Snap-On MMBX Plug to Snap-On MMBX Plug Cable RG174 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Snap-On MMBX Plug to Snap-On MMBX Plug Cable RG174 Coax FMCA1431

URL: https://www.fairviewmicrowave.com/mmbx-plug-mmbx-plug-cable-rg174-coax-fmca1431-p.aspx









STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Snap-On MMBX Plug to Snap-On MMBX Plug Cable	FMCA1431			CAGE CODE 3FKR5		
RG174 Coax	CAD FILE 062217	SHEET 1 OF 1	SCAL	E N/A	SIZE A	9999