



Snap-On MMBX Plug to SMA Male Cable RG174 Coax

Fairview Microwave's MMBX cable assemblies are part of our full line of RF interconnects available for same-day shipping. These MMBX cable assemblies are designed for test applications or connection of your MMBX system components. With a high frequency range up to 3 GHz, this family of MMBX cables can also be used to connect your panels to PCB's with between series options like MMBX-to-SMA, MMBX-to-N or MMBX-to-TNC assemblies. There are hundreds of possible cable assembly configurations to choose from, all available same day.

This MMBX cable assembly datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave not only has many MMBX cable assembly options, but also a wide selection of RF, microwave and millimeter wave cable assemblies which allows RF designers to customize their configurations to whatever is required. Whether the need is to provide an I/O for a board design or simply create a custom cable assembly configuration, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom RF cable assemblies for you and ship same day.

Electrical Specifications

Description	Min	Т	ур	Max	U	nits
Frequency Range	DC			1,000	N	ЛHz
VSWR				1.4:1		
Return Loss		-15.56		(dB	
Velocity of Propagation		66		%		
Capacitance	31.1 [102.03]		pF/ft	pF/ft [pF/m]		

Performance by Frequency

	_	=				
Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.06	0.08	0.14	0.22	0.32	dB/ft
	0.2	0.26	0.46	0.72	1.05	dB/m

dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.315 in [8 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

RG174 50 Ohms Stranded Copper Clad Steel, Silver PE 1



Configuration:

- Snap-On MMBX Plug
- SMA Male
- RG174


Features:

- Max. Operating Frequency of 1
- Snap-On mating

Applications:

- General Purpose MMBX Test
- PCB Testing
- Low Profile MMBX Cable Jumpers
- PCB-to-Panel Connection

Cable Diagram:



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shield Layer 1 Jacket Material Jacket Diameter Tinned Copper Braid PVC, Black 0.11 in [2.79 mm]

Connectors

Description	Connecto	Connector 2			
Туре	MMBX Plug		SMA Male		
Specification			MIL-STD-348A		
Impedance	50 Ohms		50 Ohms		
Connection Method	Snap-O	n			
Mating Cycles	100				
Contact Material & Plating	Beryllium Copp	er, Gold	d Brass, Gold		
Contact Plating Spec.			30 µin minimun		
Dielectric Type	PTFE		PTFE		
Outer Cond Material & Plat	ing Brass, Go	old			
Body Material & Plating	Brass, Go	old	Brass, Nickel		
Body Plating Spec.			100 µin minimum		
Coupling Nut Material & Pla	ating		Brass, Nickel		
Coupling Nut Plating Spec.			100 µin minimum		
Hex Size			5/16 inch		
Torque			3 in-lbs [0.34 N		

Mechanical Specification Notes:

Environmental Specific

TemperatureOperating Range

-40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA1436 - xx uu | cm = Centimeters | chlank> = Inches | Length

Example: FMCA1436-12 = 12 inches long cable

FMCA1436-100cm = 100 cm long cable

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Snap-On MMBX Plug to SMA Male Cable RG174 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Snap-On MMBX Plug to SMA Male Cable RG174 Coax FMCA1436

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/mmbx-plug-sma-male-cable-rg174-coax-fmca1436-p.aspx

stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.
arising out of the use of any part or documentation.





.X ±0.2 .XX ±0.01 .XXX ±0.005

STANDARD TOLERANCES

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
Snap-On MMBX Plug to SMA Male Cable RG174 Coax	FMCA1436				CAGE CODE 3FKR5		
	CAD FILE 062217	SHEET 1 OF 1	SCAL	E N/A	SIZE A	9999	