



Slide-On BMA Jack 2 Hole Flange to SMA Male Cable RG405 Type .086 Coax

The BMA jack slide-on 2 hole flange to SMA male cable using RG405 type .086 coax, part number FMCA1595, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMA cable assembly has a jack to male gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1595 BMA jack to SMA male cable assembly operates to 18 GHz. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	Units
Frequency Range	DC			18	GHz
VSWR				1.5:1	
Return Loss				15.56	dB

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.22	0.28	0.46	0.75	1.13	dB/ft
	0.72	0.92	1.51	2.46	3.71	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.75 in [19.05 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Outer Conductor Material and Plating

FM-SR086CU 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper

Repeated Minimum Bend Radius 0.05 in [1.27 mm]



Configuration:

- Slide-On BMA Jack 2 Hole Flange
- SMA Male
- FM-SR086CU

Features:

Max Frequency 18 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description		Connect	or 1		Connector 2		
		BMA Jack			SMA Male		
Mount Method		2 Hole Flange					
Impedance		50 Ohms 50 Ohms		S			
Connection Method	nection Method)n				
Contact Material & Plating		Beryllium Copper, Gold		Brass, Gold ove	r Nickel		
Contact Plating Spec.		51.18µ in. minimum					
Dielectric Type		PTFE		PTFE			
Outer Cond Material & Plat	ing	Beryllium Cop	per, Go	old			
Body Material & Plating		Stainless Ste	el, Gol	d	Brass, Gold ove	r Nickel	
Body Plating Spec.		19.68µ in. m	inimur	n			
Coupling Nut Material & Pla	ating				Passivated Stainl	ess Steel	
Hex Size				5/16 inc	h		
Torque				8 in-lbs [0.9	Nm]		

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Example: FMCA1595-12 = 12 inches long cable

FMCA1595-100cm = 100 cm long cable





Slide-On BMA Jack 2 Hole Flange to SMA Male Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Jack 2 Hole Flange to SMA Male Cable RG405 Type .086 Coax FMCA1595


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/bma-jack-sma-male-cable-rg405-type-.086-coax-fmca1595-p.aspx

described	herein. It	may be	necessar	y to ma	ke modifica	ations to the	e part a	nd/or t	ne docume	ntation of tl	he part	, in order
to implem	ent improv	ements.	Fairview	/ Microw	ave reserve	es the right	to mak	e such (changes as	required. I	Jnless (otherwise
stated, all	l specificat	ions are	nominal.	Fairvie	w Microwa	ve does not	make	any rep	resentation	or warran	ty rega	rding the
						purpose, a	nd Fair	view Mi	crowave do	es not assi	ume an	y liability
arising ou	t of the us	e of any	part or de	ocument	tation.							







STANDARD TOLERANCES ,X ±0.2 ,XX ±0.01 ,XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME, 3. DIMENSIONS ARE IN INCHES [mm],							
Slide-On BMA Jack 2 Hole Flange to SMA Male Cable RG405 Type .086 Coax	DWG NO FMCA15	CAGE CODE 3FKR5						
NG403 Type .000 Coax	CAD FILE 12/19/17	SHEET	SCAL	LE N/A SIZE /	CN2245			