

FMCA1610 DATA SHEET

Slide-On BMA Jack 2 Hole Flange to RA SMP Female Cable RG405 Type .086 Coax

The BMA jack slide-on 2 hole flange to RA SMP female cable using RG405 type .086 coax, part number FMCA1610, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMP cable assembly has a jack to female gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1610 BMA jack to SMP female cable assembly operates to 18 GHz. The right angle SMP interface on the FM-SR086CU cable allows for easier connections in tight spaces. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

•				
Description	Min	Ту	p Max	Units
Frequency Range	DC		18	GHz
VSWR			1.5:1	
Return Loss			15.56	dB

Performance by Frequency							
Description	F1	F2	F3	F4	F5	Units	
Frequency	1	2	4.5	9	22	GHz	
Insertion Loss (Typ.)	0.22	0.28	0.46	5 0.74	1.25	dB/ft	

0.92

Electrical Specification Notes:

0.72

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

1.51

2.43

4.1

dB/m

Mechanical Specifications

Cable Assembly Diameter	0.75 in [19.05 mm]
Cable	

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Outer Conductor Material and Plating

FM-SR086CU 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper



Configuration:

- Slide-On BMA Jack 2 Hole Flange
- SMP Female Right Angle
- FM-SR086CU

Features:

• Max Frequency 18 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Repeated Minimum Bend Radius

0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2	
Туре	BMA Jack	BMA Jack SMP Female	
Mount Method	2 Hole Flange	2 Hole Flange	
Specification		MIL-STD-348	
Impedance	50 Ohms	50 Ohms	
Connection Method	Slide-On		
Contact Material & Plating	Beryllium Copper, G	old Beryllium Copper, Gold	
Contact Plating Spec.	51.18µ in. minimur	m MIL-G-45204	
Dielectric Type	PTFE	PTFE	
Outer Cond Material & Plati	ng Beryllium Copper, G	old	
Body Material & Plating	Stainless Steel, Go	ld Beryllium Copper, Gold	
Body Plating Spec.	19.68µ in. minimur	m MIL-G-45204	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Environmental Specifications

Temperature Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:










Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Slide-On BMA Jack 2 Hole Flange to RA SMP Female Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Jack 2 Hole Flange to RA SMP Female Cable RG405 Type .086 Coax FMCA1610


URL: https://www.fairviewmicrowave.com/bma-jack-ra-smp-female-cable-rg405-type-.086-coax-fmca1610-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
Slide-On BMA Jack 2 Hole Flange to RA SMP Female Cable RG405 Type .086 Coax	dwg no FMCA1610			CAGE CODE 3FKR5	
	CAD FILE 12/20/17	SHEET	SCAL	.e n/a size a	CN2245

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689