



Slide-On BMA Jack 2 Hole Flange to RA SMA Male Cable FM-SR141TBJ Coax

The BMA jack slide-on 2 hole flange to RA SMA male cable using FM-SR141TBJ coax, part number FMCA1623, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMA cable assembly has a jack to male gender configuration with 50 ohm formable FM-SR141TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semirigid assemblies since they are hand formable. The FMCA1623 BMA jack to SMA male cable assembly operates to 10 GHz. The right angle SMA interface on the FM-SR141TBJ cable allows for easier connections in tight spaces. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Т | ур | Max | ι | Inits |
|-------------------------|-----|-------|----------------------|-------|----------|----------|
| Frequency Range | DC | | | 10 | | GHz |
| VSWR | | | | 1.5:1 | | |
| Return Loss | | | | 15.56 | | dB |
| Velocity of Propagation | | - | 70 | | | % |
| RF Shielding | 100 | | | | | dB |
| Group Delay | | 1.43 | 1.43 [4.69] ns/ft [r | | t [ns/m] | |
| Capacitance | | 29 [9 | 95.14] | | pF/f | t [pF/m] |
| | | | | | | |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 0.5 | 1 | 2.5 | 5 | 10 | GHz |
| Insertion Loss (Typ.) | 0.08 | 0.12 | 0.18 | 0.28 | 0.42 | dB/ft |
| | 0.26 | 0.39 | 0.59 | 0.92 | 1.38 | dB/m |

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.74 in [18.8 mm]

Cable

Cable TypeFM-SR141TBJImpedance50 OhmsInner Conductor TypeSolid



Configuration:

- Slide-On BMA Jack 2 Hole Flange
- SMA Male Right Angle
- FM-SR141TBJ

Features:

- Max Frequency 10 GHz
- Shielding Effectivity > 100 dB
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter Copper Clad Steel, Silver

PTFE 1

Tinned Copper Braid

FEP, Black

0.161 in [4.09 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius 0.315 in [8 mm] 1.575 in [40.01 mm]

Connectors

| Description | Connector 1 | Connector 2 | | |
|------------------------------|------------------------|-----------------------------|--|--|
| Туре | BMA Jack | SMA Male | | |
| Mount Method | 2 Hole Flange | | | |
| Impedance | 50 Ohms | 50 Ohms | | |
| Connection Method | Slide-On | | | |
| Contact Material & Plating | Beryllium Copper, G | old Brass, Gold over Nickel | | |
| Dielectric Type | PTFE | PTFE | | |
| Outer Cond Material & Platin | ng Beryllium Copper, G | Gold | | |
| Body Material & Plating | Brass, Tri-Metal | Brass, Gold over Nickel | | |
| Coupling Nut Material & Plat | Plating Passivated Sta | | | |
| Hex Size | | 5/16 inch | | |
| Torque | | 8 in-lbs [0.9 Nm] | | |
| | | | | |

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Example: FMCA1623-12 = 12 inches long cable

FMCA1623-100cm = 100 cm long cable





Slide-On BMA Jack 2 Hole Flange to RA SMA Male Cable FM-SR141TBJ Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Jack 2 Hole Flange to RA SMA Male Cable FM-SR141TBJ Coax FMCA1623


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/bma-jack-ra-sma-male-cable-fm-sr141tbj-coax-fmca1623-p.aspx

| described | herein. It | may be i | necessar | y to ma | ke modifica | ations to th | e part a | nd/or tl | ne documer | itation of the p | art, in order |
|-------------|--------------|-----------|-----------|----------|-------------|--------------|----------|----------|-------------|------------------|---------------|
| to implem | ent improv | ements. | Fairview | / Microw | ave reserv | es the right | to mak | e such o | changes as | required. Unle | ss otherwise |
| stated, all | specificati | ons are r | nominal. | Fairvie | w Microwa | ve does no | t make | any rep | resentation | or warranty re | egarding the |
| | | | | | | purpose, a | and Fair | view Mi | crowave do | es not assume | any liability |
| arising ou | t of the use | of any p | art or do | ocument | tation. | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |







STANDARD TOLERANCES
,X ±0.2

XX ±0.01 XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | | |
|---|---|-----------------|------|---------------|--------|--|--|
| Slide-On BMA Jack 2 Hole Flange to RA SMA Male Cable FM-SR141TBJ Coax | DWG NO FMCA16 | CAGE CODE 3FKR5 | | | | | |
| Cable III SKIHIIBS COUX | CAD FILE 12/22/17 | SHEET | SCAL | LE N/A SIZE A | CN2245 | | |