



Slide-On RA BMA Jack 2 Hole Flange to RA Slide-On BMA Jack 2 Hole Flange Cable FM-SR141TBJ Coax

The RA BMA jack slide-on 2 hole flange to RA BMA jack slide-on 2 hole flange cable using FM-SR141TBJ coax, part number FMCA1615, from Fairview Microwave is instock and ships same day. This Fairview BMA to BMA cable assembly has a jack to jack gender configuration with 50 ohm formable FM-SR141TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly preformed semi-rigid assemblies since they are hand formable. The FMCA1615 BMA jack to BMA jack cable assembly operates to 12.4 GHz. The right angle BMA interfaces on the FM-SR141TBJ cable allow for easier connections in tight spaces. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			12.4		GHz
VSWR				1.5:1		
Return Loss				15.56		dB
Velocity of Propagation		-	70			%
RF Shielding	100					dB
Group Delay		1.43 [4.69] ns/fl		t [ns/m]		
Capacitance		29 [9	95.14]		pF/f	t [pF/m]
Operating Voltage (AC)				350	١	/rms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	12.4	GHz
Insertion Loss (Typ.)	0.08	0.12	0.18	0.27	0.47	dB/ft
	0.26	0.39	0.59	0.89	1.54	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.37 in [9.4 mm]

Cable

Cable Type FM-SR141TBJ Impedance 50 Ohms



Configuration:

- Slide-On BMA Jack Right Angle 2
 Hole Flange
- Slide-On BMA Jack Right Angle 2 Hole Flange
- FM-SR141TBJ

Features:

- Max Frequency 12.4 GHz
- Shielding Effectivity > 100 dB
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fay: (972) 649-6689

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1

Jacket Material FEP, Black Jacket Diameter

One Time Minimum Bend Radius 0.315 in [8 mm] Repeated Minimum Bend Radius 1.575 in [40.01 mm]

Solid

Copper Clad Steel, Silver PTFE

1 Tinned Copper Braid

0.161 in [4.09 mm]

Connectors

Description	Connector 1	Connector 2
Туре	BMA Jack	BMA Jack
Mount Method	2 Hole Flange	2 Hole Flange
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	Slide-On
Contact Material & Plating	Beryllium Copper, G	old Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plati	ng Beryllium Copper, G	old Beryllium Copper, Gold
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range -40 to +100 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2018


REV 1.1 Page 2 of 5

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Part Number Configuration:

FMCA1615 - xx uu

| cm = Centimeters |
| chlark > = Inches |
| Length

Example: FMCA1615-12 = 12 inches long cable

FMCA1615-100cm = 100 cm long cable





Slide-On RA BMA Jack 2 Hole Flange to RA Slide-On BMA Jack 2 Hole Flange Cable FM-SR141TBJ Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On RA BMA Jack 2 Hole Flange to RA Slide-On BMA Jack 2 Hole Flange Cable FM-SR141TBJ Coax FMCA1615


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: https://www.fairviewmicrowave.com/ra-bma-jack-ra-bma-jack-cable-fm-sr141tbj-coax-fmca1615-p.aspx

described herein. I	t may be necessar	y to make	e modifications t	to the part a	nd/or th	e documentation o	f the part,	in order
to implement impro	vements. Fairview	/ Microway	ve reserves the	right to make	e such c	hanges as required	. Unless o	therwise
stated, all specifica	tions are nominal.	Fairview	Microwave doe	s not make a	any rep	resentation or warr	anty regar	ding the
suitability of the pa				se, and Fair	view Mi	crowave does not a	ssume an	y liability
arising out of the us	se of any part or do	ocumenta	tion.					







STANDARD TOLERANCES ,X ±0,2 ,XX ±0,01

XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME, 3. DIMENSIONS ARE IN INCHES [mm].					
Slide-On RA BMA Jack 2 Hole Flange to RA Slide-On BMA Jack 2 Hole Flange Cable FM-SR141TBJ Coax	DWG NO FMCA16	CAGE CODE 3FKR5				
BMA Jack 2 Hole Hange Cable FM SKI411BJ Coax	CAD FILE 11/27/2017	SHEET	SCAL	LE N/A SIZE A	CN2245	