

FMCA1647 DATA SHEET

Slide-On BMA Plug Bulkhead to TNC Male Cable LMR-100 Coax

The BMA plug slide-on bulkhead to TNC male cable using LMR-100 coax, part number FMCA1647, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to TNC cable assembly has a plug to male gender configuration with 50 ohm flexible LMR-100A-PVC coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1647 BMA plug to TNC male cable assembly operates to 2.5 GHz. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Inits
Frequency Range	DC			2.5		GHz
VSWR				1.4:1		
Return Loss				15.56		dB
Velocity of Propagation		e	56			%
RF Shielding	90					dB
Group Delay		1.54	[5.05]		ns/f	t [ns/m]
Capacitance		30.8 [101.05	5]	pF/f	t [pF/m]
Inductance		0.077	[0.25]	uH/f	t [uH/m]
DC Resistance Inner Cor	ductor	81 [2	65.75]		Ω/100	0ft [Ω/Km]
DC Resistance Outer Cor	nductor	9.5 [31.17]		Ω/1000ft [Ω/Km]		
Jacket Spark				2,000	١	/rms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	2.5	GHz
Insertion Loss (Typ.)	0.07	0.12	0.16	0.24	0.4	dB/ft
	0.23	0.39	0.52	0.79	1.31	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly Diameter

0.6 in [15.24 mm]



Configuration:

- Slide-On BMA Plug Bulkhead
- TNC Male
- LMR-100A-PVC

Features:

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

LMR-100A-PVC 50 Ohms Solid Copper Clad Steel PE 2 Aluminum Tape Tinned Copper Braid PVC, Black 0.11 in [2.79 mm]

One Time Minimum Bend Radius0.25 in [6.35 mm]Repeated Minimum Bend Radius1 in [25.4 mm]Bending Moment0.1 lbs-ft [0.14 N-m]Flat Plate Crush10 lbs/in [0.18 Kg/mm]Tensile Strength15 lbs [6.8 Kg]

Connectors

Description	Connector 1	Connector 2
Туре	BMA Plug	TNC Male
Mount Method	Bulkhead	
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Spec.	51.18µ in. minimum	
Dielectric Type	PTFE	Teflon
Outer Cond Material & Plati	ng Passivated Stainless Steel	
Body Material & Plating	Passivated Stainless Steel	Brass, Silver
Coupling Nut Material & Pla	iting	Brass, Silver
Hex Size	8 mm	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:





Typical Performance Data








Slide-On BMA Plug Bulkhead to TNC Male Cable LMR-100 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Slide-On BMA Plug Bulkhead to TNC Male Cable LMR-100 Coax FMCA1647

URL: https://www.fairviewmicrowave.com/bma-plug-tnc-male-cable-Imr100-coax-fmca1647-p.aspx









 TITLE
 Slide-On BMA Plug Bulkhead to TNC Male Cable LMR-100 Coax
 DWG NO

 DWG NO
 CAGE CODE

 FMCA1647
 3FKR5

 CAD FILE 12/29/17
 SHEET
 SCALE N/A
 SIZE A
 CN2245