



# Plenum Low PIM SMA Male to NEX10 Male Cable SPP-250-LLPL Coax Using Times Microwave Parts

The SMA male to NEX10 male cable using SPP-250-LLPL coax, part number FMCA1928, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to NEX10 cable assembly has a male to male gender configuration with 50 ohm corrugated SPP-250-LLPL coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA1928 SMA male to NEX10 male cable assembly operates to 5.8 GHz. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Тур		Max	Units		
Frequency Range	DC			5.8		GHz	
VSWR				1.4:1			
Velocity of Propagation			76			%	
RF Shielding	100					dB	
Passive Intermodulation		-1	165	-160		dBc	
Capacitance	pacitance		27 [88.58]			pF/ft [pF/m]	
Inductance		0.067 [0.22]		.]	uH/ft [uH/m]		
DC Resistance Inner Conductor		3 [9.84]			Ω/1000ft [Ω/Km]		

## **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.45	0.7	1	2.5	5.8	GHz
Insertion Loss (Max	a.) 0.038	0.048	0.057	0.094	0.148	dB/ft
	0.12	0.16	0.19	0.31	0.49	dB/m

**Electrical Specification Notes:** 

PIM test results vary between cables

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.15 dB for the SMA male connector and 0.1\*SQRT(FGHz) dB for the NEX10 male connector.

## **Mechanical Specifications**

**Cable Assembly** 

Lenath\*

0 in [0 mm]



## **Configuration:**

- SMA Male
- TC-SPP250-SM-LP
- NEX10 Male
- TC-250-NX10M-LP
- SPP-250-LLPL

## **Features:**

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- 100% Tested with PIM Test Results Marked on Cable
- UL910 Plenum Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

## **Applications:**

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing

# Cable Diagram:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Length

**Cable** 

Cable Type SPP-250-LLPL
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PTFE

Number of Shields
Shield Layer 1

Outer Conductor Material and Plating

Outer Conductor Diameter

Jacket Material

Jacket Diameter

One Time Minimum Bend Radius

Bending Moment

PTFE
1
Helically Corrugated Copper Tube

Copper

0.25 in [6.35 mm]

FEP, Blue

0.28 in [7.11 mm]

1.25 in [31.75 mm] 0.8 lbs-ft [1.08 N-m]

#### **Connectors**

Description	Connector 1	Connector 2			
Туре	SMA Male	NEX10 Male			
Impedance	50 Ohms	50 Ohms			
Mating Cycles		500			
Contact Material & Plating	Brass, Silver	Brass, Silver			
Contact Plating Spec.	196 µin	100 μin			
Dielectric Type	PTFE	PTFE			
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal			
Body Plating Spec.	118 µin	100 μin			
Coupling Nut Material & Pla	ting Brass, Tri-Metal	Brass, Tri-Metal			
Coupling Nut Plating Spec.	118 µin	100 μin			
Torque	10 in-lbs 1.13 Nr	13.28 in-lbs 1.5 Nm			

#### **Environmental Specifications**

Temperature

Operating Range -55 to +200 deg C
Storage Range -55 to +200 deg C
Plenum Rating UL910

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

#### **How to Order**

Part Number Configuration:

FMCA1928 - xx uu

| cm = Centimeters
| chlank> = Inches

Example: FMCA1928-12 = 12 inches long cable

FMCA1928-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1.0 Page 2 of 4





Plenum Low PIM SMA Male to NEX10 Male Cable SPP-250-LLPL Coax Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Plenum Low PIM SMA Male to NEX10 Male Cable SPP-250-LLPL Coax Using Times Microwave Parts FMCA1928

The information contained in this document is accurate to the best of our knowledge and representative of the part


URL: https://www.fairviewmicrowave.com/low-pim-sma-male-nex10-male-cable-spp250llpl-coax-fmca1928-p.aspx

described	herein. It may	y be necessar	y to ma	ke modification	ns to the part a	and/or t	he documentation of the	part, in order
to implem	ent improveme	ents. Fairview	Microw	ave reserves	the right to mak	e such	changes as required. Unl	ess otherwise
							resentation or warranty	
					urpose, and Fair	view Mi	crowave does not assum	e any liability
arising out	t of the use of	any part or do	ocument	ation.				

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave an INFINIT® brand	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
TITLE	DWG NO FMCA	CAGE CODE 3FKR5				
Plenum Low PIM SMA Male to NEX10 Male Cable SPP- 250-LLPL Coax Using Times Microwave Parts	CAD FILE 06/05/19	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361