

FMCA2058 DATA SHEET

Outdoor Rated Low PIM 4.3-10 Male to 4.3-10 Male Cable SPO-375 Coax Using Times Microwave Parts

The 4.3-10 male to 4.3-10 male cable using SPO-375 coax, part number FMCA2058, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 cable assembly has a male to male gender configuration with 50 ohm corrugated SPO-375 coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -158 dBc. The FMCA2058 4.3-10 male to 4.3-10 male cable assembly operates to 3 GHz. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	T	ур	Max	ι	Inits	
Frequency Range	DC			3		GHz	
VSWR				1.4:1			
Velocity of Propagation		83		%			
Passive Intermodulation				-158		dBc	
Capacitance		24 [78.74]		pF/fl	t [pF/m	— 1]	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	3		GHz
Insertion Loss (Max.)	0.03	0.04	0.06	0.08		dB/ft
	0.1	0.13	0.2	0.26		dB/m

Electrical Specification Notes:

PIM test results vary between cables

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm] Weight 0.33 lbs [149.69 g]

Cable

Cable Type SPO-375 Impedance 50 Ohms



- 4.3-10 Male
- TC-SPO375-4310M-LP
- 4.3-10 Male
- TC-SPO375-4310M-LP
- SPO-375

Features:

- Max Frequency 3 GHz
- Low PIM: -158 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

Cable Diagram:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1

Outer Conductor Material and Plating

Jacket Diameter

Jacket Material

1.75 in [44.45 mm]

0.43 in [10.92 mm]

Copper Clad Aluminum

Helically Corrugated Copper Tube

Solid

Foam PE

Copper PE, Black

One Time Minimum Bend Radius

Connectors

Description	Connector 1	Connector 2	
Туре	4.3-10 Male	4.3-10 Male	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Brass, Silver	Brass, Silver	
Contact Plating Spec.	200 μin	200 μin	
Dielectric Type	PTFE	PTFE	
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Body Plating Spec.	80 μin	80 μin	
Coupling Nut Material & Pla	iting Brass, Nickel	Brass, Nickel	
Coupling Nut Plating Spec.	200 μin	200 μin	

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C



Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2058 - xx uu cm = Centimeters

dlank> = Inches Length

Example: FMCA2058-12 = 12 inches long cable

FMCA2058-100cm = 100 cm long cable





Outdoor Rated Low PIM 4.3-10 Male to 4.3-10 Male Cable SPO-375 Coax Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Outdoor Rated Low PIM 4.3-10 Male to 4.3-10 Male Cable SPO-375 Coax Using Times Microwave Parts FMCA2058

URL: https://www.fairviewmicrowave.com/low-pim-4.3-10-male-4.3-10-male-cable-spo375-coax-fmca2058-p.aspx









Outdoor Rated Low PIM 4.3-10 Male to 4.3-10 Male Cable SPO-375 Coax Using Times Microwave Parts