

## Outdoor Rated 4.3-10 Male to 7/16 DIN Male Low PIM Cable Using SPO-375 Coax Using Times Microwave Parts

The 4.3-10 male to 7/16 DIN male cable using SPO-375 coax, part number FMCA2060, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm corrugated SPO-375 coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -158 dBc. The FMCA2060 4.3-10 male to 7/16 DIN male cable assembly operates to 3 GHz. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-158	dBc
Capacitance		24 [78.74]		pF/ft [pF/m]

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Unit
Frequency	0.5	1	2	3		GHz
Insertion Loss (Max.)	0.03	0.04	0.06	0.08		dB/ft
	0.1	0.13	0.2	0.26		dB/m

#### Electrical Specification Notes:

PIM test results vary between cables

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as  $0.1 * \text{SQRT}(\text{FGHz})$  dB for the 4.3-10 connector and 0.1 dB for the 7/16 DIN connector.

### Mechanical Specifications

#### Cable Assembly

Description	Min	Typ	Max	Units
Cable Outer Diameter		0.43		
One Time Min Bend Radius	1.75			in



### Configuration:

- Connector 1: TC-SPO375-4310M-LP (4.3-10 Male)
- Connector 2: TC-SPP375-716M-LP (7/16 DIN Male)
- Cable: SPO-375

### Features:

- Max Frequency 3 GHz
- Low PIM: -158 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

### Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Cable Characteristics**

Component	Specification
Cable Type	SPO-375
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Mat. & Plat.	Copper Clad Aluminum
Dielectric Type	Foam PE
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube
Outer Conductor Mat. & Plat.	Copper
Jacket Material	PE, Black

**Connector Characteristics**

Description	Connector 1	Connector 2
Type	4.3-10 Male	7/16 DIN Male
Impedance	50 Ohms	50 Ohms
Contact Mat. & Plat.	Brass, Silver	Brass, Silver
Contact Plating Spec.	200 µin	5 µin
Dielectric Type	PTFE	PTFE
Body Mat. & Plat.	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Spec.	80 µin	3 µin
Coupling Nut Mat. & Plat.	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Plating Spec.	200 µin	3 µin

**Environmental Specifications**

Description	Specification
Temperature Operating Range	-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**Typical Performance Data**



**How to Order**

Part Number Configuration:

**FMCA2060 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length


Example: FMCA2060-12 = 12 inches long cable  
 FMCA2060-100cm = 100 cm long cable

Outdoor Rated 4.3-10 Male to 7/16 DIN Male Low PIM Cable Using SPO-375 Coax Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Outdoor Rated 4.3-10 Male to 7/16 DIN Male Low PIM Cable Using SPO-375 Coax Using Times Microwave Parts FMCA2060](#)

URL: <https://www.fairviewmicrowave.com/4.3-10-female-n-female-cable-spo375-coax-fmca2060-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<p><b>Fairview Microwave</b> an INFINIT<sup>®</sup> brand</p>	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
	TITLE Outdoor Rated 4.3-10 Male to 7/16 DIN Male Low PIM Cable Using SPO-375 Coax Using Times Microwave Parts		DWG NO FMCA2060		CAGE CODE 3FKR5			
CAD FILE	07/19/19	SHEET	1 OF 1	SCALE	N/A	SIZE	A	7361