



SMA Male to SSMA Male Cable FM-SR086TB Coax

The SMA male to SSMA male cable using FM-SR086TB coax, part number FMCA2102, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMA cable assembly has a male to male gender configuration with 50 ohm formable FM-SR086TB coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Min | Тур | Max | Units |
|-----|------------|------|-------------|
| | 69.5 | | % |
| | 29 [95.14] | p | F/ft [pF/m] |
| | Min | 69.5 | 69.5 |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 1 | 2 | 4.5 | 9 | 18 | GHz |
| Insertion Loss (Typ.) | 0.23 | 0.31 | 0.51 | 0.76 | 1.12 | dB |
| | 0.75 | 1.02 | 1.67 | 2.49 | 3.67 | |

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector

Mechanical Specifications

Cable Assembly

Length* Diameter 0 in [0 mm] 0.312 in [7.92 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Outer Conductor Material and Plating
Outer Conductor Diameter

FM-SR086TB 50 Ohms Solid Copper Clad Steel, Silver PTFE Tinned Copper Composite Braid 0.086 in [2.18 mm]



Configuration:

- SMA Male
- SSMA Male
- FM-SR086TB

Features:

- 69.5% Phase Velocity
- Dimensionally and electrically the same as standard, solid outer conductor semi-rigid coax
- Cable may be formed by hand and does not require special tools to bend
- May be formed more than once without damaging the outer conductor
- High RF Shielding >100 dB
- 100% Hi-pot and continuity tested
- 100% VSWR tested to max frequency of assembly
- Standard and custom lengths ship the same day

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------|------------------------|--------------------|
| Туре | SMA Male | SSMA Male |
| Specification | | MIL-C-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Mating Cycles | 500 | |
| Contact Material & Plating | Brass, Gold | Gold |
| Contact Plating Spec. | 50μ in. minimum, MIL-G | -45204 MIL-G-45204 |
| Dielectric Type | PTFE | Teflon |
| Body Material & Plating | Stainless Steel, Gol | d Brass, Gold |
| Body Plating Spec. | MIL-G-45204 | MIL-G-45204 |
| Coupling Nut Material & Pla | nting Brass, Nickel | Brass, Nickel |
| Coupling Nut Plating Spec. | QQ-N-290 | |
| Hex Size | 5/16 in. | 1/4 in. |
| Torque | 5 in-lbs 0.57 Nm | 3 in-lbs 0.34 Nm |
| | | |

Mechanical Specification Notes:


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.

How to Order



SMA Male to SSMA Male Cable FM-SR086TB Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to SSMA Male Cable FM-SR086TB Coax FMCA2102

URL: https://www.fairviewmicrowave.com/sma-male-ssma-male-cable-fm-sr086tb-coax-fmca2102-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





