



4.3-10 Male to 4.3-10 Male Cable 1/4 inch Superflexible Coax

The 4.3-10 male to 4.3-10 male cable using 1/4 inch superflexible coax, part number FMCA2237, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 cable assembly has a male to male gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. The FMCA2237 4.3-10 male to 4.3-10 male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			6		GHz
VSWR				1.5:1		
Velocity of Propagation		8	32			%
RF Shielding	120					dB
Passive Intermodulation				-150		dBc
Capacitance		24.4	[80.05]		pF/f	t [pF/m]
Inductance		0.059	[0.19]		uH/f	t [uH/m]
DC Resistance Inner Cor	ductor	3.2	[10.5]		Ω/100	Oft [Ω/Km]
DC Resistance Outer Cor	nductor	2.53	8 [8.3]		Ω/100	0ft [Ω/Km]
Jacket Spark				2,000	١	/rms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.016	0.026	0.039	0.057	0.107	dB/ft
	0.05	0.09	0.13	0.19	0.35	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2dB connector loss.

Mechanical Specifications

Cable Assembly

Diameter 0.94 in [23.88 mm]

Cable

Cable Type Impedance Inner Conductor Type 1/4" Superflexible 50 Ohms Solid



Configuration:

- 4.3-10 Male
- 4.3-10 Male
- 1/4" Superflexible

Features:

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

Applications:

- General Purpose
- Laboratory Use
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Inner Conductor Material and Plating

Dielectric Type Number of Shields

Shield Layer 1 Helically Corrugated Copper Tube

Jacket Material PE, Black

Jacket Diameter 0.303 in [7.7 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius

Typical Flex Cycles

Tensile Strength

0.5 in [12.7 mm] 1 in [25.4 mm]

Copper Clad Aluminum

20

PE (F)

1

79 lbs [35.83 Kg]

Connectors

Description	Connector 1	Connector 2		
Туре	4.3-10 Male	4.3-10 Male		
Specification	IEC 61169-54	IEC 61169-54		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Silver	Brass, Silver		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal		
Coupling Nut Material & Platin	g Brass, Tri-Metal	Brass, Tri-Metal		

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2237 - xx uu | cm = Centimeters | chlank> = Inches | Length

Example: FMCA2237-12 = 12 inches long cable

FMCA2237-100cm = 100 cm long cable





4.3-10 Male to 4.3-10 Male Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 4.3-10 Male to 4.3-10 Male Cable 1/4 inch Superflexible Coax FMCA2237

URL: https://www.fairviewmicrowave.com/4.3-10-male-4.3-10-male-pe-1-4-sfhc-cable-assembly-FMCA2237-p.aspx







