

FMCA2261 DATA SHEET

Low PIM NEX10 Male to RA NEX10 Male Cable 1/4 inch Superflexible Coax

The NEX10 male to RA NEX10 male cable using 1/4 inch superflexible coax, part number FMCA2261, from Fairview Microwave is in-stock and ships same day. This Fairview NEX10 to NEX10 cable assembly has a male to male gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The FMCA2261 NEX10 male to NEX10 male cable assembly operates to 6 GHz. The right angle NEX10 interface on the 1/4" Superflexible cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Т | ур | Max | Units |
|-------------------------|-----|---|----|-------|-------|
| Frequency Range | DC | | | 6 | GHz |
| VSWR | | | | 1.5:1 | |
| Velocity of Propagation | | 8 | 32 | | % |
| RF Shielding | 120 | | | | dB |
| Passive Intermodulation | | | | -150 | dBc |

| Capacitance | | 24.4 [80.05] | pF/ft [pF/m] |
|-------------------------|---------|--------------|-----------------|
| Inductance | | 0.059 [0.19] | uH/ft [uH/m] |
| DC Resistance Inner Cor | nductor | 3.2 [10.5] | Ω/1000ft [Ω/Km] |
| DC Resistance Outer Cor | nductor | 2.53 [8.3] | Ω/1000ft [Ω/Km] |
| Jacket Spark | | 2,0 | 00 Vrms |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-------|-------|-------|-------|-------|-------|
| Frequency | 0.1 | 0.25 | 0.5 | 1 | 3 | GHz |
| Insertion Loss (Typ.) | 0.016 | 0.026 | 0.039 | 0.057 | 0.107 | dB/ft |
| | 0.05 | 0.09 | 0.13 | 0.19 | 0.35 | dB/m |

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.25dB connector loss.

Mechanical Specifications

Cable Assembly

Diameter 0.47 in [11.94 mm]

Cable

Cable Type 1/4" Superflexible



Configuration:

- NEX10 Male
- NEX10 Male Right Angle
- 1/4" Superflexible

Features:

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Impedance 50 Ohms Inner Conductor Type Solid

Inner Conductor Material and Plating Copper Clad Aluminum

Dielectric Type PE (F)
Number of Shields 1

Shield Layer 1 Helically Corrugated Copper Tube

Jacket Material PE, Black

Jacket Diameter 0.303 in [7.7 mm]

One Time Minimum Bend Radius 0.5 in [12.7 mm]
Repeated Minimum Bend Radius 1 in [25.4 mm]

Typical Flex Cycles

Tensile Strength 79 lbs [35.83 Kg]

Connectors

| Description | Connector 1 | Connector 2 | | |
|----------------------------|------------------|------------------|--|--|
| Туре | NEX10 Male | NEX10 Male | | |
| Specification | NEX10 | NEX10 | | |
| Impedance | 50 Ohms | 50 Ohms | | |
| Contact Material & Plating | Brass, Silver | Brass, Silver | | |
| Dielectric Type | PTFE | PTFE | | |
| Body Material & Plating | Brass, Tri-Metal | Brass, Tri-Metal | | |
| | | | | |

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2261 - xx

uu

cm = Centimeters
<black> = Inches

Length

Example: FMCA2261-12 = 12 inches long cable

FMCA2261-100cm = 100 cm long cable





Low PIM NEX10 Male to RA NEX10 Male Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low PIM NEX10 Male to RA NEX10 Male Cable 1/4 inch Superflexible Coax FMCA2261

URL: https://www.fairviewmicrowave.com/low-pim-nex10-male-ra-nex10-male-cable-fm-1-4-sfhc-coax-fmca2261-p.aspx







