



# Low PIM RA NEX10 Male to NEX10 Female Cable 1/4 inch Superflexible Coax

The RA NEX10 male to NEX10 female cable using 1/4 inch superflexible coax, part number FMCA2265, from Fairview Microwave is in-stock and ships same day. This Fairview NEX10 to NEX10 cable assembly has a male to female gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The FMCA2265 NEX10 male to NEX10 female cable assembly operates to 6 GHz. The right angle NEX10 interface on the 1/4" Superflexible cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Т	ур	Max	U	Inits
Frequency Range	DC			6		GHz
VSWR				1.5:1		
Velocity of Propagation		8	32			%
RF Shielding	120					dB
Passive Intermodulation				-150		dBc

Capacitance		24.4 [80.05]		pF/ft [pF/r	n]
Inductance		0.059 [0.19]		uH/ft [uH/r	m]
DC Resistance Inner Cor	ductor	3.2 [10.5]		Ω/1000ft [Ω/	Km]
DC Resistance Outer Cor	nductor	2.53 [8.3]		Ω/1000ft [Ω/	Km]
Jacket Spark			2,000	Vrms	

#### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.016 0.05	0.026 0.09	0.039 0.13	0.057 <b>0.19</b>	0.107 <b>0.3</b> 5	dB/ft dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.25dB connector loss.

#### **Mechanical Specifications**

**Cable Assembly** 

Diameter 0.47 in [11.94 mm]

Cable

Cable Type 1/4" Superflexible



# **Configuration:**

- NEX10 Male Right Angle
- NEX10 Female
- 1/4" Superflexible

## **Features:**

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

# **Applications:**

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Impedance 50 Ohms Inner Conductor Type Solid

Inner Conductor Material and Plating Copper Clad Aluminum

Dielectric Type PE (F)
Number of Shields 1

Shield Layer 1 Helically Corrugated Copper Tube

Jacket Material PE, Black

Jacket Diameter 0.303 in [7.7 mm]

One Time Minimum Bend Radius 0.5 in [12.7 mm]
Repeated Minimum Bend Radius 1 in [25.4 mm]

Typical Flex Cycles

Tensile Strength 79 lbs [35.83 Kg]

### **Connectors**

Description	Connector	· 1	Connector 2	
Туре	NEX10 Mal	le	NEX10 Female	
Specification	NEX10		NEX10	
Impedance	50 Ohms		50 Ohms	
Contact Material & Plating	Brass, Silve	er		
Dielectric Type	PTFE		PTFE	
Outer Cond Material & Plati	ing		Bronze, Silver	
Body Material & Plating	Brass, Tri-Me	etal	Brass, Tri-Metal	

## **Environmental Specifications**

Temperature

Operating Range -40 to +85 deg C

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data** 

Notes:

**How to Order** 

Part Number Configuration: FMCA2265 - xx uu

cm = Centimeters
<black> = Inches

Length

Example: FMCA2265-12 = 12 inches long cable

FMCA2265-100cm = 100 cm long cable





Low PIM RA NEX10 Male to NEX10 Female Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low PIM RA NEX10 Male to NEX10 Female Cable 1/4 inch Superflexible Coax FMCA2265

URL: https://www.fairviewmicrowave.com/low-pim-ra-nex10-male-nex10-female-cable-fm-1-4-sfhc-coax-fmca2265-p. aspx







