

FMCA2271 DATA SHEET

Low PIM RA 2.2-5 Male to RA 2.2-5 Male Cable 1/4 inch Superflexible Coax

The RA 2.2-5 male to RA 2.2-5 male cable using 1/4 inch superflexible coax, part number FMCA2271, from Fairview Microwave is in-stock and ships same day. This Fairview 2.2-5 to 2.2-5 cable assembly has a male to male gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The FMCA2271 2.2-5 male to 2.2-5 male cable assembly operates to 6 GHz. The right angle 2.2-5 interfaces on the 1/4" Superflexible cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	U	nits
Frequency Range	DC			6		GHz
VSWR				1.5:1		
Velocity of Propagation		3	32			%
RF Shielding	120					dB
Passive Intermodulation				-150		dBc

Capacitance		24.4 [80.05]		pF/ft [pF/r	n]
Inductance		0.059 [0.19]		uH/ft [uH/ı	m]
DC Resistance Inner Cor	nductor	3.2 [10.5]		Ω/1000ft [Ω/	Km]
DC Resistance Outer Cor	nductor	2.53 [8.3]		Ω/1000ft [Ω/	Km]
Jacket Spark			2,000	Vrms	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.016 0.05	0.026 0.09	0.039 0.13	0.057 0.19	0.107 0. 35	dB/ft dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.3dB connector loss.

Mechanical Specifications

Cable Assembly

Diameter 0.69 in [17.53 mm]

Cable

Cable Type 1/4" Superflexible



Configuration:

- 2.2-5 Male Right Angle
- 2.2-5 Male Right Angle
- 1/4" Superflexible

Features:

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields

Shield Layer 1

Jacket Material

Jacket Diameter

One Time Minimum Bend Radius Repeated Minimum Bend Radius

Typical Flex Cycles

Tensile Strength

50 Ohms Solid

Copper Clad Aluminum

PE (F) 1

Helically Corrugated Copper Tube

PE, Black

0.303 in [7.7 mm]

0.5 in [12.7 mm] 1 in [25.4 mm]

20

79 lbs [35.83 Kg]

Connectors

Description	Connector 1	Connector 2				
Туре	2.2-5 Male	2.2-5 Male				
Specification	2.2-5	2.2-5				
Impedance	50 Ohms	50 Ohms				
Contact Material & Plating	Brass, Silver	Brass, Silver				
Dielectric Type	PTFE	PTFE				
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal				
Coupling Nut Material & Pla	ting Brass, Tri-Metal	Brass, Tri-Metal				

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2271 - xx

cm = Centimeters

lank> = Inches

Length

Example: FMCA2271-12 = 12 inches long cable

FMCA2271-100cm = 100 cm long cable





Low PIM RA 2.2-5 Male to RA 2.2-5 Male Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low PIM RA 2.2-5 Male to RA 2.2-5 Male Cable 1/4 inch Superflexible Coax FMCA2271


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/low-pim-ra-2.2-5-male-ra-2.2-5-male-cable-fm-1-4-sfhc-coax-fmca2271-p. aspx

to implen	nent improvement	s. Fairview	Microw	ave reserv	es the righ	nt to mak	e such	changes	as requ	ired. Un	ess ot	herwise
	I specifications are											
suitability	of the part descr	ibed hereir	for any	particular	purpose,	and Fair	view M	icrowave	does r	ot assum	e any	liability
arising ou	it of the use of any	part or do	cument	ation.								







TOLERANCES: CABLE LENGTH (L) TOLERANCES: THE INFORMATION AND an INFINIT® brand DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
FAIRVIEW MICROWAVE CORPORATION
ALL RIGHTS RESERVED. L ≤ 12 [305] = +1 [25] / -0 .X = ±.2 [5.08] FRACTIONS .XX = ±.02 [.51] ± 1/32 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 TITLE .XXX = ±.005 [.13] ANGLES ± 1° 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0 SHEET OF Low PIM RA 2.2-5 Male to RA 2.2-5 Male Cable 1/4 1 inch Superflexible Coax SCALE ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. N/A CAGE CODE DRAWN BY ITEM NO. SIZE REV 3FKR5 K.DANG FMCA2271 Α T-Rev.D