

FMCA2331

Configuration

Connector 1: 2.2-5 Male
Connector 2: 2.2-5 Female
Cable Type: TFT-5G-402
Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- · Double Shielded
- · FEP Jacket
- 100 Mating Cycles

Applications

- · General Purpose
- · Laboratory Use

- Low PIM Applications
- Indoor and Outdoor Use
- · Plenum Rated Applications

Description

The 2.2-5 male to 2.2-5 female cable using TFT-5G-402 coax, part number FMCA2331, from Fairview Microwave is in-stock and ships same day. This Fairview 2.2-5 to 2.2-5 cable assembly has a male to female gender configuration with 50 ohm flexible TFT-5G-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2331 2.2-5 male to 2.2-5 female cable assembly operates to 3 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				





FMCA2331

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.07	0.08	0.11	0.2	0.3	dB/ft
	0.23	0.26	0.36	0.66	0.98	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

Width/Diameter 0.665 in [16.89 mm]

Cable

Cable Type TFT-5G-402 Impedance 50 Ohms Inner Conductor Type Solid

Inner Conductor Material and Plating Copper PTFE

Dielectric Type Number of Shields Jacket Material FEP, Blue

0.16 in [4.06 mm] Jacket Diameter One Time Minimum Bend Radius 0.75 in [19.05 mm]



FMCA2331

Connectors

Description	Connector 1	Connector 2
Туре	2.2-5 Male	2.2-5 Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	100	100
Contact Material and Plating	Beryllium Copper, Silver	Beryllium Copper, Silver
Contact Plating Specification	200 μin	200 μin
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Beryllium Copper, Silver
Outer Conductor Plating Specification		100 μin
Body Material and Plating	Brass, Silver	Brass, Silver
Body Plating Specification	100 μin	100 μin
Coupling Nut Material and Plating	Brass, Tri-Metal	
Coupling Nut Plating Specification	100 μin	
Torque	26 in-lbs 2.94 Nm	26 in-lbs 2.94 Nm

Environmental Specifications

Operating Range Temperature

-40 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:





FMCA2331

Typical Performance Data

How to Order

Part Number Configuration:

FMCA2331 - xx uu

Unit of Measure:
cm = Centimeters

chlank> = Inches

Length
Base Number

Example: FMCA2331-12 = 12 inches long cable

FMCA2331-100cm = 100 cm long cable

2.2-5 Male to 2.2-5 Female Low PIM Cable Using TFT-5G-402 Coax Using Times Microwave Components from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.2-5 Male to 2.2-5 Female Low PIM Cable Using TFT-5G-402 Coax Using Times Microwave Components FMCA2331

URL: https://www.fairviewmicrowave.com/low-pim-2.2-5-male-to-2.2-5-female-cable-tft-5g-402-coax-using-times-micro-wave-components-fmca2331-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

