

FMCA2364 DATA SHEET

Low PIM 2.2-5 Male to 4.3-10 Female Cable 1/4 inch Superflexible Coax

The 2.2-5 male to 4.3-10 female cable using 1/4 inch superflexible coax, part number FMCA2364, from Fairview Microwave is in-stock and ships same day. This Fairview 2.2-5 to 4.3-10 cable assembly has a male to female gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2364 2.2-5 male to 4.3-10 female cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	т	ур	Max	ι	Jnits
Frequency Range	DC			6		GHz
VSWR				1.4:1		
Velocity of Propagation		8	32			%
RF Shielding	120					dB
Passive Intermodulation				-160		dBc
Capacitance		24.4	[80.05]		pF/f	t [pF/m]
Inductance		0.059	0.19]		uH/f	t [uH/m]
DC Resistance Inner Con	ductor	3.2	[10.5]		Ω/100	0ft [Ω/Km]
DC Resistance Outer Cor	nductor	2.53	8 [8.3]		Ω/100	0ft [Ω/Km]
Jacket Spark				2,000	١	/rms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.01	0.02	0.03	0.05	0.1	dB/ft
	0.03	0.07	0.1	0.16	0.33	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2dB connector loss.

Mechanical Specifications

Cable Assembly

Diameter

Cable Cable Type Impedance 0.8 in [20.32 mm]

1/4" Superflexible 50 Ohms



Configuration:

- 2.2-5 Male
- 4.3-10 Female
- 1/4" Superflexible

Features:

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Type		Solid				
Inner Conductor Material and Plating		Copper Clad Aluminum				
Dielectric Type		PE (F)				
Number of Shields		1				
Shield Layer 1		Helically Corrugated Copper Tube				
Jacket Material		PE, Black				
Jacket Diameter		0.303 in [7.7 mm]				
One Time Minimum Bend Radius		0.5 in [12.7 mm]				
Repeated Minimum Bend Radius		1 in [25.4 mm]				
Typical Flex Cycles		20				
Tensile Strength		79 lbs [35.83 Kg]				
Connectors						
Description	Connect	or 1	Connector 2			


Description	Connector 1	connector 2		
Туре	2.2-5 Male	4.3-10 Female		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Silver	Bronze, Silver		
Dielectric Type	PTFE	PTFE		
Outer Cond Material & Plati	ng	Bronze, Tri-Metal		
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal		
Coupling Nut Material & Pla	ting Brass, Tri-Metal			

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C



Example: FMCA2364-12 = 12 inches long cable FMCA2364-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





Low PIM 2.2-5 Male to 4.3-10 Female Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Low PIM 2.2-5 Male to 4.3-10 Female Cable 1/4 inch Superflexible Coax FMCA2364

URL: https://www.fairviewmicrowave.com/low-pim-2.2-5-male-4.3-10-female-cable-fm-1-4-sfhc-coax-fmca2364-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part, described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

an INFINIT© brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689