

Test Probe SMA Female 2 Hole Flange to Straight Cut Lead Cable FM-SR047TB Coax

The 50 ohm SMA Female to straight cut lead cable using FM-SR047TB coax, part number FMCA2387, from Fairview Microwave is in-stock and ships same day. Fairview Microwave's formable cable assemblies provide a convenient alternative to their semi-rigid versions, as they offer similar electrical performance but can be bent to desired shape without the use of special tools.

Fairview's hand formable test probes are convenient ready-to-use probes designed for use in testing microwave circuits. These probes are constructed of high quality hand formable coax and a SMA Female connector. The assemblies come in multiple cable diameters to help when attaching two very fine traces or into tight spaces. There are two versions including straight-cut probe ends for those that would like to customize the dimensions of the center conductor and dielectric dimensions as well as pre-stripped probe ends that are ready for immediate use. Each assembly has been RF tested to ensure VSWR specifications of the assembly are met prior to trimming. Each assembly comes in special packaging to protect the coax and pre-trimmed probe ends.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Capacitance		32 [104.99]		pF/ft [pF/r
chanical Specificati	ons			
Cable Assembly				
Weight		0.007 lbs	[3.18 g]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materia Dielectric Type Number of Shields Shield Layer 1 Jacket Diameter	al and Plating	FM-SR047 50 Ohms Solid Copper CI PTFE 1 Tinned Cc 0.047 in	ad Steel	aid



FMCA2387

Configuration:

- SMA Female 2 Hole Flange
- Straight Cut Lead
- FM-SR047TB

Features:

- Max Frequency 18 GHz
- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 18 GHz
- 100% High Pot Tested to 500V
- 0.047 Diameter Formable coax
- Individually packed in protective tube

Applications:

- General Purpose
- Test & Measurement
- Laboratory Use
- RF Test Lead for Measurements up to 18 GHz/Testing of Individual Function or Subsection of an RF Circuit Board
- Inject Signals for Test and Verification

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT^C brand



Connectors

	Connector 1	Connector 2	
Туре	SMA Female	Straight Cut Lead	
Mount Method	2 Hole Flange		
Specification	MIL-STD-348		
Impedance	50 Ohms		
Contact Material & Plating	Beryllium Copper, Gold		
Contact Plating Spec.	MIL-G-45204		
Dielectric Type	Teflon		
Body Material & Plating	Stainless Steel, Gold		
Body Plating Spec.	MIL-G-45204		
otted and Other Data			
Notes: • Values at 25°C, sea level. w to Order			
Notes: • Values at 25°C, sea level.	in: FM	CA2387 - xx	uu cm = Centimet <blank> = Inches Length</blank>

Test Probe SMA Female 2 Hole Flange to Straight Cut Lead Cable FM-SR047TB Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Test Probe SMA Female 2 Hole Flange to Straight Cut Lead Cable FM-SR047TB Coax FMCA2387


URL: https://www.fairviewmicrowave.com/test-probe-sma-female-straight-cut-lead-cable-fm-sr047tb-coax-fmca2387-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT[©] brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689