

### **FMCA2479**

### Configuration

Connector 1: 4.1/9.5 Mini DIN Male
Connector 2: N Male Right Angle

Cable Type: TFT-5G-402Coax Flex Type: Flexible

#### **Features**

- · Max Frequency 3 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- · Double Shielded
- · FEP Jacket

### **Applications**

- General Purpose
- · Laboratory Use

- · Low PIM Applications
- · Indoor and Outdoor Use
- · Plenum Rated Applications

### **Description**

The 4.1/9.5 Mini DIN male to RA type N male cable using TFT-5G-402 coax, part number FMCA2479, from Fairview Microwave is in-stock and ships same day. This Fairview 4.1/9.5 Mini DIN to type N cable assembly has a male to male gender configuration with 50 ohm flexible TFT-5G-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2479 4.1/9.5 Mini DIN male to type N male cable assembly operates to 3 GHz. The right angle type N interface on the TFT-5G-402 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				



### **FMCA2479**

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.035	0.057	0.083	0.117	0.207	dB/ft
	0.11	0.19	0.27	0.38	0.68	dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

### **Mechanical Specifications**

**Cable Assembly** 

Width/Diameter 0.866 in [22 mm]

Weight lbs [0 g]

Cable

Cable Type TFT-5G-402 Impedance 50 Ohms

Inner Conductor Type Solid Inner Conductor Material and Plating Copper Dielectric Type **PTFE** 

Number of Shields FEP, Blue Jacket Material

Jacket Diameter 0.16 in [4.06 mm] One Time Minimum Bend Radius 0.75 in [19.05 mm]



### **FMCA2479**

#### **Connectors**

Description	Connector 1	Connector 2
Туре	4.1/9.5 Mini DIN Male	N Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	5 μm	5 μm
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	2 μm	3 μm
Coupling Nut Material and Plating	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Plating Specification	5 μm	3 μm
Torque	106 in-lbs 11.98 Nm	10 in-lbs 1.13 Nm

### **Environmental Specifications**

**Operating Range Temperature** 

-40 to +85 deg C

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**


Notes:



### **FMCA2479**

### **Typical Performance Data**

### **How to Order**



Example: FMCA2479-12 = 12 inches long cable

FMCA2479-100cm = 100 cm long cable

Low PIM 4.1/9.5 Mini DIN Male to RA N Male Cable TFT-5G-402 Coax Using Times Microwave Components from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Low PIM 4.1/9.5 Mini DIN Male to RA N Male Cable TFT-5G-402 Coax Using Times Microwave Components FMCA2479

URL: https://www.fairviewmicrowave.com/product/rf-cable-assemblies/low-pim-4.1-9.5-mini-din-male-to-ra-n-male-ca-ble-tft-5g-402-coax-using-times-microwave-components-fmca2479.html

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.