Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components

FMCA2485

Configuration

- Connector 1: 4.3-10 Male
- Connector 2: 7/16 DIN Female 4 Hole Flange
- Cable Type: TFT-402-LF
- · Coax Flex Type: Flexible

Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

- Low PIM Applications
- Indoor and Outdoor Use
- Plenum Rated Applications

Description

The 4.3-10 male to 7/16 DIN female 4 hole flange cable using TFT-402-LF coax, part number FMCA2485, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 7/16 DIN cable assembly has a male to female gender configuration with 50 ohm flexible TFT-402-LF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2485 4.3-10 male to 7/16 DIN female cable assembly operates to 5.8 GHz. Our RF cable assembly with 7/16 DIN 4 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				





Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components



FMCA2485

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.057	0.083	0.117	0.19	0.295	dB/ft
	0.19	0.27	0.38	0.62	0.97	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1*SQRT(FGHz) dB for the male connector and 0.1 dB for the female connector.

Mechanical Specifications

Cable Assembly

Width/Diameter Weight	1.26 in [32 mm] lbs [0 g]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Jacket Material Jacket Diameter One Time Minimum Bend Radius	TFT-402-LF 50 Ohms Solid Copper PTFE 2 FEP, Blue 0.16 in [4.06 mm] 0.75 in [19.05 mm]

© 2023 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.

Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components



FMCA2485

Connectors

Description	Connector 1	Connector 2
Туре	4.3-10 Male	7/16 DIN Female 4 Hole Flange
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	200 µin	5 µm
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Outer Conductor Plating Specification		3 µm
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 µin	3 µm
Coupling Nut Material and Plating	Brass, Tri-Metal	
Coupling Nut Plating Specification	80 µin	
Torque	44 in-lbs 4.97 Nm	22.083 ft-lbs 29.95 Nm

Environmental Specifications

Operating Range Temperature

-55 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:


Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components

FMCA2485

Typical Performance Data

How to Order

Part Number Configuration:



Example: FMCA2485-12 = 12 inches long cable FMCA2485-100cm = 100 cm long cable

Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components FMCA2485

URL: https://www.fairviewmicrowave.com/product/rf-cable-assemblies/low-pim-4.3-10-male-7-16-din-female-cable-tft-402-lf-coax-fmca2485.html

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

© 2023 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.



FMCA2485 CAD Drawing Low PIM 4.3-10 Male to 7/16 DIN Female 4 Hole Flange Cable TFT-402-LF Coax Using Times Microwave Components

© 2023 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.