The Right Parts, Right Away

Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components

FMCA2486

Configuration

- Connector 1: 4.3-10 Male
- Connector 2: 7/16 DIN Male
- Cable Type: TFT-5G-402
- · Coax Flex Type: Flexible

Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

- Low PIM Applications
- Indoor and Outdoor Use
- · Plenum Rated Applications

Description

The 4.3-10 male to 7/16 DIN male cable using TFT-5G-402 coax, part number FMCA2486, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm flexible TFT-5G-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2486 4.3-10 male to 7/16 DIN male cable assembly operates to 5.8 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				



Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components

FMCA2486

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.057	0.083	0.117	0.19	0.295	dB/ft
	0.19	0.27	0.38	0.62	0.97	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1*SQRT(FGHz) dB for the 4.3-10 connector and 0.1 dB for the 7/16 DIN connector.

Mechanical Specifications

Cable Assembly

Weight
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Jacket Material Jacket Diameter One Time Minimum Bend Radius

1.25 in [31.75 mm] lbs [0 g]

TFT-5G-402 50 Ohms Solid Copper PTFE 2 FEP, Blue 0.16 in [4.06 mm] 0.75 in [19.05 mm]

© 2023 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.



Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components

FMCA2486

Connectors

Description	Connector 1	Connector 2
Туре	4.3-10 Male	7/16 DIN Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	200 µin	5 µm
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 µin	3 µm
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80 µin	3 μm
Torque	44 in-lbs 4.97 Nm	22.083 ft-lbs 29.95 Nm

Environmental Specifications

Operating Range Temperature

-55 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:





The Right Parts, Right Away

Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components

FMCA2486

Typical Performance Data

How to Order

Part Number Configuration:

FMCA2486 - xx uu Unit of Measure: cm = Centimeters <blank> = Inches Length Base Number

Example: FMCA2486-12 = 12 inches long cable FMCA2486-100cm = 100 cm long cable

Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components FMCA2486

URL: https://www.fairviewmicrowave.com/product/rf-cable-assemblies/low-pim-4.3-10-male-to-7-16-din-male-cable-tft-5g-402-coax-using-times-microwave-components-fmca2486.html

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.





FMCA2486 CAD Drawing Low PIM 4.3-10 Male to 7/16 DIN Male Cable TFT-5G-402 Coax Using Times Microwave Components

© 2023 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.