

Fire Rated Low PIM 7/16 DIN Male to N Male Cable SPF-375 Coax in 7 Inch Using Times Microwave Parts

The 7/16 DIN male to type N male 7 inch cable using SPF-375 coax, part number FMCA2551, from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to type N cable assembly has a male to male gender configuration with 50 ohm corrugated SPF-375 coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2551 7/16 DIN male to type N male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			6		GHz
VSWR				1.4:1		
Velocity of Propagation		8	33			%
Passive Intermodulation				-160		dBc
Capacitance		24 [78.74]		pF/f	t [pF/m]

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	4	6	GHz
Insertion Loss (Typ.)	0.03	0.04	0.0 <mark>69</mark>	0.09	0.116	dB

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

Length* Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Outer Conductor Material and Plating Jacket Material Jacket Diameter 7 in [177.8 mm] 0.282 lbs [127.91 g]

SPF-375 50 Ohms Solid Copper Clad Aluminum Foam PE 1 Copper FRPE, Black 0.435 in [11.05 mm]

FMCA2551 DATA SHEET



Configuration:

- 7/16 DIN Male
- N Male
- SPF-375

Features:

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- FRPE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- CMR Riser Rated Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

Cable Diagram:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT³ brand



One Time Minimum Bend Radius

1.75 in [44.45 mm]

Connectors

Description	Connect	or 1:	Connector 2	
Туре	7/16 DIN	Male	N Male	
Impedance	50 Ohr	ns	50 Ohms	
Contact Material & Plating	Brass, S	lver	Brass, Silver	
Contact Plating Spec.	200 µ	n	200 µin	
Dielectric Type	PTFE		PTFE	
Outer Cond Material & Plati	ng		Brass, Tri-Metal	
Outer Cond Plating Spec.			100 µin	
Body Material & Plating	Brass, Tri-	Metal		
Body Plating Spec.	100 µ	'n		
Coupling Nut Material & Pla	ting Brass, Tri-	Metal	Brass, Tri-Metal	
Coupling Nut Plating Spec.	100 µ	n	100 µin	
Torque			9.74 in-lbs 1.1 Nm	

Environmental Specifications

Temperature Operating Range

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2551 - xx



Example: FMCA2551-12 = 12 inches long cable FMCA2551-100cm = 100 cm long cable





Fire Rated Low PIM 7/16 DIN Male to N Male Cable SPF-375 Coax in 7 Inch Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Fire Rated Low PIM 7/16 DIN Male to N Male Cable SPF-375 Coax in 7 Inch Using Times Microwave Parts FMCA2551

URL: https://www.fairviewmicrowave.com/fire-rated-low-pim-7-16-din-male-to-n-male-cable-spf-375-coax-in-7-inchusing-times-microwave-parts-fmca2551-p.aspx









301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689