



## Outdoor Rated Low PIM 7/16 DIN Female to N Male Cable SPO-375 Coax in 7 Inch Using Times Microwave Parts

The 7/16 DIN female to type N male 7 inch cable using SPO-375 coax, part number FMCA2569, from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to type N cable assembly has a female to male gender configuration with 50 ohm corrugated SPO-375 coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2569 7/16 DIN female to type N male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### **Electrical Specifications**

Description	Min	T	ур І	Мах	U	Inits
Frequency Range	DC			6		GHz
VSWR			1	.4:1		
Velocity of Propagation		8	33			%
Passive Intermodulation			-	160		dBc
Capacitance		24 [7	78.74]		pF/ft	[pF/m]

#### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	4	6	GHz
Insertion Loss (Typ.)	0.03	0.043	0.069	0.09	0.116	dB

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1\*SQRT(FGHz) dB per connector.

#### **Mechanical Specifications**

#### **Cable Assembly**

Jacket Diameter

 Length\*
 7 in [177.8 mm]

 Weight
 0.3575 lbs [162.16 g]

#### Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Outer Conductor Material and Plating
Jacket Material

SPO-375
50 Ohms
Solid
Copper Clad Aluminum
Foam PE
1
Copper
PE, Black

0.43 in [10.92 mm]



## **Configuration:**

- 7/16 DIN Female
- N Male
- SPO-375

#### Features:

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

## **Applications:**

- General Purpose
- Laboratory Use
- Low PIM Applications
- Outdoor Rated Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

# Cable Diagram:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





One Time Minimum Bend Radius

1.75 in [44.45 mm]

#### **Connectors**

Description	Connect	Connector 1		Connector 2	
Туре	7/16 DIN F	7/16 DIN Female		N Male	
Impedance	50 Ohr	50 Ohms		50 Ohms	
Mating Cycles	500	500			
Contact Material & Plating	Phosphor Bron	Phosphor Bronze, Silver		Brass, Silver	
Contact Plating Spec.	200 µi	200 μin		200 μin	
Dielectric Type	PTFE		PTFE		
Outer Cond Material & Plating			Brass, Tri-Me	tal	
Outer Cond Plating Spec.			100 μin		
Body Material & Plating	Brass, Tri-	Metal			
Body Plating Spec.	100 μί	100 μin			
Coupling Nut Material & Pla	iting		Brass, Tri-Me	tal	
Coupling Nut Plating Spec.			100 μin		
Torque			9.74 in-lbs 1.1	. Nm	

### **Environmental Specifications**

**Temperature** 

Operating Range

-40 to +85 deg C


**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **How to Order**

Part Number Configuration:



Example: FMCA2569-12 = 12 inches long cable

FMCA2569-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 4





Outdoor Rated Low PIM 7/16 DIN Female to N Male Cable SPO-375 Coax in 7 Inch Using Times Microwave Parts from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Outdoor Rated Low PIM 7/16 DIN Female to N Male Cable SPO-375 Coax in 7 Inch Using Times Microwave Parts FMCA2569

URL: https://www.fairviewmicrowave.com/outdoor-rated-low-pim-7-16-din-female-to-n-male-cable-spo-375-coax-in-7-inch-using-times-microwave-parts-fmca2569-p.aspx









301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689