



TNC Female to BNC Male Cable Using RG223 Coax

The TNC female to BNC male cable using RG223 coax, part number FMCA2684, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to BNC cable assembly has a female to male gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Тур	Max	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

RG223

Mechanical Specifications

Cable Assembly

Weight 0.079 lbs [35.83 g]

Cable

Cable Type

Impedance 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper, Silver Dielectric Type Number of Shields Shield Layer 1 Silver Plated Copper Braid Shield Layer 2 Silver Plated Copper Braid Jacket Material PVC, Black Jacket Diameter 0.209 in [5.31 mm]

Repeated Minimum Bend Radius 1 in [25.4 mm]



Configuration:

- TNC Female
- BNC Male
- RG223

Features:

- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2	
Туре	TNC Female	BNC Male	
Specification		MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating		Brass, Gold	
Contact Plating Spec.		30 µin minimum	
Dielectric Type		PTFE	
Body Material & Plating	Brass, Nickel	Brass, Nickel	
Body Plating Spec.		100 µin minimum	
Coupling Nut Material & Plating		Brass, Nickel	
Coupling Nut Plating Spec.		100 µin minimum	

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:

Values at 25°C, sea level.

How to Order

Part Number Configuration:



Example: FMCA2684-12 = 12 inches long cable

FMCA2684-100cm = 100 cm long cable

TNC Female to BNC Male Cable Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: TNC Female to BNC Male Cable Using RG223 Coax FMCA2684

URL: https://www.fairviewmicrowave.com/tnc-female-to-bnc-male-cable-rg223-coax-and-rohs-fmca2684-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





