

FMCA2988 DATA SHEET

2.4mm Male to 2.4mm Female Cable Tinned Aluminum RG405 Type .086 Coax

The 2.4mm male to 2.4mm female cable using Tinned Aluminum RG405 type .086 coax, part number FMCA2988, from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm cable assembly has a male to female gender configuration with 50 ohm semi-rigid FM-SR086ALTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2988 2.4mm male to 2.4mm female cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Ту	р Мах	Units
Frequency Range	DC		40	GHz
VSWR			1.5:1	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2.5	5	10	20	GHz
Insertion Loss (Typ.)	0.23 0.75	0.32 1.05	0.48 1.57	0.81 2.66	1.31 4.3	dB/ft dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.034 lbs [15.42 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1

FM-SR086ALTN-STR 50 Ohms Solid Copper Clad Steel, Silver PTFE 1

Tinned Aluminum



Configuration:

- 2.4mm Male
- 2.4mm Female
- FM-SR086ALTN-STR

Features:

Max Frequency 40 GHz

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2	
Туре	2.4mm Male	2.4mm Female	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold	
Contact Plating Spec.	MIL-G-45204, Type II, Class	1MIL-G-45204, Type II, Class	
Dielectric Type	PPO	PPO	
Body Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel	
Body Plating Spec.	ASTM B689	QQ-P-35	
Coupling Nut Material & Plati	ng Passivated Stainless Steel		
Coupling Nut Plating Spec.	SAE-AMS-2700		
Hex Size	5/16 in.		
Torque	8 in-lbs 0.9 Nm		

Mechanical Specification Notes:

Maximum length using the straight semi rigid coax is 5ft. For lengths greater than 5ft, please contact us


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.

How to Order



2.4mm Male to 2.4mm Female Cable Tinned Aluminum RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 2.4mm Male to 2.4mm Female Cable Tinned Aluminum RG405 Type .086 Coax FMCA2988

URL: https://www.fairviewmicrowave.com/2.4mm-male-to-2.4mm-female-cable-tinned-aluminum-rg405-type-.086-coax-fmca2988-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





