

2.92mm Male to 2.92mm Female Cable RG405 Type .086 Coax in 200 CM

The 2.92mm male to 2.92mm female 200 cm cable using RG405 type .086 coax, part number FMCA2959-200CM, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.92mm cable assembly has a male to female gender configuration with 50 ohm semi-rigid FM-SR086CU-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2959-200CM 2.92mm male to 2.92mm female cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------|------|--------------|-------|--------------|
| Frequency Range | DC | | 40 | GHz |
| VSWR | | | 1.5:1 | |
| Velocity of Propagation | | 69.5 | | % |
| RF Shielding | -110 | | | dB |
| Capacitance | | 29.4 [96.46] | | pF/ft [pF/m] |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|-------|-------|
| Frequency | 2.5 | 5 | 10 | 20 | 40 | GHz |
| Insertion Loss (Typ.) | 2.28 | 3.33 | 5.45 | 8.08 | 15.95 | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.


Mechanical Specifications

Cable Assembly

| | |
|---------|---------------------|
| Length* | 78.74 in [200 cm] |
| Weight | 0.103 lbs [46.72 g] |

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | FM-SR086CU-STR |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Outer Conductor Material and Plating | Copper |



Configuration:

- 2.92mm Male
- 2.92mm Female
- FM-SR086CU-STR

Features:

- Max Frequency 40 GHz
- Shielding Effectivity > -110 dB
- 69.5% Phase Velocity

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Repeated Minimum Bend Radius 0.05 in [1.27 mm]

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------|------------------------------------|---------------|
| Type | 2.92mm Male | 2.92mm Female |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Beryllium Copper, Gold over Nickel | |
| Contact Plating Spec. | 50 µin minimum | |
| Dielectric Type | PCTFE | |
| Body Material & Plating | Beryllium Copper, Gold over Nickel | |
| Body Plating Spec. | 50 µin minimum | |
| Coupling Nut Material & Plating | Passivated Stainless Steel | |
| Hex Size | 5/16 inch | |
| Torque | 8 in-lbs 0.9 Nm | |

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2959 - xx uu

cm = Centimeters
 <blank> = Inches

Length

Example: FMCA2959-12 = 12 inches long cable
 FMCA2959-100cm = 100 cm long cable

2.92mm Male to 2.92mm Female Cable RG405 Type .086 Coax in 200 CM from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: [2.92mm Male to 2.92mm Female Cable RG405 Type .086 Coax in 200 CM FMCA2959-200CM](https://www.fairviewmicrowave.com/2.92mm-male-to-2.92mm-female-cable-rg405-type-.086-coax-fmca2959-200cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/2.92mm-male-to-2.92mm-female-cable-rg405-type-.086-coax-fmca2959-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| REVISIONS | | | |
|-----------|-----------------|------------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 07/26/2022 | AGANWANI |



NOTES:

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| | | | | | |
|--|---|---|--|---|--|
| <p>Fairview Microwave an INFINIT[®] brand</p> | UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS | | THIRD-ANGLE PROJECTION | | |
| | TOLERANCES: | | CABLE LENGTH (L) TOLERANCES: | | |
| .X = ±.2 [.508] FRACTIONS ± 1/32 .XX = ±.02 [.51] ± 1/32 .XXX = ±.005 [.13] ANGLES ± 1° | | L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0 | | THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED. SHEET 1 OF 1 | |
| TITLE 2.92mm Male to 2.92mm Female Cable RG405 Type .086 Coax in 200 CM | | | ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. SCALE N/A | | |
| SIZE A | CAGE CODE 3FKR5 | DRAWN BY PSRINIVAS | ITEM NO. FMCA2959 | REV A | |

T-Rev.D