



RA QMA Male to RA QMA Male Cable Tinned Copper RG405 Type .086 Coax

The RA QMA male to RA QMA male cable using Tinned Copper RG405 type .086 coax, part number FMCA3047, from Fairview Microwave is in-stock and ships same day. This Fairview QMA to QMA cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR086CUTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA3047 QMA male to QMA male cable assembly operates to 6 GHz. The right angle QMA interfaces on the FM-SR086CUTN-STR cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Configuration:

- QMA Male Right Angle
- QMA Male Right Angle
- FM-SR086CUTN-STR

Features:

- Max Frequency 6 GHz
- 100 Mating Cycles

Applications:

- General Purpose
- Laboratory Use

Electrical Specifications

Description	Min	Т	ур М	lax	Units
Frequency Range	DC			6	GHz
VSWR			1.	5:1	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2.5	6			GHz
Insertion Loss (Typ.)	0.22	0.316	0.542			dB/ft
	0.72	1.04	1.78			dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

Shield Layer 1

Weight 0.043 lbs [19.5 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

One Time Minimum Bend Radius

FM-SR086CUTN-STR

50 Ohms Solid

Copper Clad Steel, Silver

PTFE 1

Tinned Copper

0.05 in [1.27 mm]

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Connector 1	Connector 2		
QMA Male	QMA Male		
50 Ohms	50 Ohms		
100	100		
Brass, Gold	Brass, Gold		
PTFE	PTFE		
Brass, Gold	Brass, Gold		
Brass, Nickel	Brass, Nickel		
	QMA Male 50 Ohms 100 Brass, Gold PTFE Brass, Gold		

Mechanical Specification Notes:

Maximum length using the straight semi rigid coax is 5ft. For lengths greater than 5ft, please contact us

Environmental Specifications

Temperature

Operating Range -40 to +105 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

Example: FMCA3047-12 = 12 inches long cable FMCA3047-100cm = 100 cm long cable

RA QMA Male to RA QMA Ma<mark>le Cable Tinned Co</mark>pper RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA QMA Male to RA QMA Male Cable Tinned Copper RG405 Type .086 Coax FMCA3047

URL: https://www.fairviewmicrowave.com/ra-qma-male-to-ra-qma-male-cable-tinned-copper-rg405-type-.086-coax-fmca3047-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





