



2.4mm Male to 2.4mm Male Cable Tinned Copper RG405 Type .086 Coax

The 2.4mm male to 2.4mm male cable using Tinned Copper RG405 type .086 coax, part number FMCA3049, from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR086CUTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA3049 2.4mm male to 2.4mm male cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Configuration: • 2.4mm Male

- 2.4mm Male
- FM-SR086CUTN-STR

Features:

- Max Frequency 40 GHz
- 500 Mating Cycles

Applications:

- General Purpose
- Laboratory Use

Electrical Specifications

Description	Min	Т	ур	Max	U	Inits
Frequency Range	DC			40		GHz
VSWR				1.5:1		

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	40	GHz
Insertion Loss (Typ.)	0.316	0.477	0.8	1.2	2	dB/ft
	1.04	1.56	2.62	3.94	6.56	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.029 lbs [13.15 q]

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1

One Time Minimum Bend Radius

FM-SR086CUTN-STR 50 Ohms Solid Copper Clad Steel, Silver

PTFE

Tinned Copper

0.05 in [1.27 mm]

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2	
Туре	2.4mm Male	2.4mm Male	
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500	500	
Contact Material & Plating	Beryllium Copper, Gold ove	r NickelBeryllium Copper, Gold ov	er Nicke
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Dielectric Type	PPO	PPO	
Body Material & Plating	Passivated Stainless St	teel Passivated Stainless Steel	
Body Plating Spec.	ASTM-A380	ASTM-A380	
Coupling Nut Material & Pla	ting Passivated Stainless St	teel Passivated Stainless Steel	
Coupling Nut Plating Spec.	ASTM-A380	ASTM-A380	
Hex Size	5/16 inch	5/16 inch	
Torque	8 in-lbs 0.9 Nm	8 in-lbs 0.9 Nm	

Mechanical Specification Notes:

Maximum length using the straight semi rigid coax is 5ft. For lengths greater than 5ft, please contact us

Environmental Specifications

Temperature

Operating Range

-55 to +100 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA3049 - xx uu | cm = Centimeters | chlank> = Inches | Length

Example: FMCA3049-12 = 12 inches long cable

FMCA3049-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 4





2.4mm Male to 2.4mm Male Cable Tinned Copper RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 2.4mm Male to 2.4mm Male Cable Tinned Copper RG405 Type .086 Coax FMCA3049

URL: https://www.fairviewmicrowave.com/2.4mm-male-to-2.4mm-male-cable-tinned-copper-rg405-type-.086-coax-fm-ca3049-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





