



VITA 67 Mini SMP Male to 2.4mm Male Cable FM-P047HF Coax

FMCA9722


Configuration

· Connector 1: Mini SMP Male · Connector 2: 2.4mm Male Cable Type: FM-P047HF · Coax Cable Group: 2

· Coax Flex Type: Flexible

Features

- · Max Frequency 40 GHz
- · Shielding Effectivity > 90 dB
- 70% Phase Velocity
- · Standard MIL-STD-348 SMPM interface
- · Push-on/snap-on mating style for quick installation
- · Mini SMP (SMPM) Female compatible with VITA 67 (4-port) and (8-port) blocks
- Mini SMP (SMPM) Male Compatible with VITA 67 (4-port) and (8port) blocks



Applications

- · General Purpose
- · Laboratory Use
- · Scientific research

- High-reliability, high-density for aerospace Ground base station & communication & defense application
 - systems, avionics, radar systems

Description

The Mini SMP male to 2.4mm male cable using FM-P047HF coax, part number FMCA9722, from Fairview Microwave is in-stock and ships same day. This Fairview Mini SMP to 2.4mm cable assembly has a male to male gender configuration with 50 ohm flexible coax. Fairview Microwave's VITA 67 assemblies are high-density, high-performance RF cable assemblies that fit into VITA 67 blocks and attach to the PCB board which makes it ideal for applications where tight bends and flexure is required. The FMCA9722 Mini SMP male to 2.4mm male cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.45:1	
Velocity of Propagation		70		%
RF Shielding	90			dB



VITA 67 Mini SMP Male to 2.4mm Male Cable FM-P047HF Coax

FMCA9722

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		29 [95.14]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	40	GHz
Insertion Loss (Typ.)	0.539	0.786	1.169	1.754	2.683	dB/ft
	1.77	2.58	3.84	5.75	8.8	dB/m

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Weight 0.052 lbs [23.59 g]

Cable

Cable TypeFM-P047HFImpedance50 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Copper, Silver

Dielectric Type FEP

Shield Layer 1 Silver Plated Copper Tape

Connectors

Description	Connector 1	Connector 2	
Туре	Mini SMP Male	2.4mm Male	
Impedance	50 Ohms	50 Ohms	
Configuration	Straight	Straight	
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Nickel	
Contact Plating Specification	ASTM B488	50 μin minimum	
Body Material and Plating	Brass, Gold	Beryllium Copper, Gold over Nickel	
Body Plating Specification	ASTM B488	50 μin minimum	

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:





VITA 67 Mini SMP Male to 2.4mm Male Cable FM-P047HF Coax



FMCA9722

Values at 25°C, sea level.

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9722 - xx uu

Unit of Measure:
cm = Centimeters

Length
Base Number

Example: FMCA9722-12 = 12 inches long cable

FMCA9722-100cm = 100 cm long cable

VITA 67 Mini SMP Male to 2.4mm Male Cable FM-P047HF Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: VITA 67 Mini SMP Male to 2.4mm Male Cable FM-P047HF Coax FMCA9722

URL: https://www.fairviewmicrowave.com/vita-67-mini-smp-male-to-2.4mm-male-cable-fm-p047hf-coax-fmca9722-p. aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

