

10KV Male to 10KV Female Bulkhead Cable RG303HV Coax

The 10KV male to 10KV female bulkhead cable using RG303HV coax, part number FMCA9764, from Fairview Microwave is in-stock and ships same day. This Fairview 10KV to 10KV cable assembly has a male to female gender configuration with 50 ohm RG303HV coax. Our RF cable assembly with 10KV bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. Our 10kv high voltage RF cable assemblies are designed to handle higher voltages and minimize the risk of electric shock. Both the connectors used in this cable assemblies have recessed contact design to withstand unmated higher voltage. These cable assemblies are commonly used in applications where high voltage transmission and RF signal integrity are critical. These cable assemblies are constructed with high-quality insulation materials capable of withstanding higher voltages, ensuring safety and preventing electrical breakdown. Our cable assemblies are built with durable and flexible materials to withstand harsh environmental conditions and repetitive movements, ensuring reliable performance over extended periods.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Velocity of Propagation		69		%
Operating Voltage (DC)			10,000	Vdc
Test Voltage (DC)			15,000	V

Electrical Specification Notes:
 Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Weight 0.126 lbs [57.15 g]

Cable

Cable Type RG303HV
 Impedance 50 Ohms
 Inner Conductor Material and Plating Silver, Copper Clad Aluminum
 Dielectric Type FEP
 Number of Shields 1
 Jacket Material FEP
 Jacket Diameter 0.169 in [4.29 mm]
 Repeated Minimum Bend Radius 0.788 in [20.02 mm]



Configuration:

- 10KV Male
- 10KV Female Bulkhead
- RG303HV

Features:

- 69% Phase Velocity
- FEP Jacket
- Voltage rating of 10kV
- Recessed Contacts

Applications:

- General Purpose
- Laboratory Use
- High voltage power supplies/Amplifiers
- Nuclear instrumentation
- Test and measurement equipment

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	10KV Male	10KV Female Bayonet
Mount Method		Bulkhead
Specification	MIL-STD-202	MIL-STD-202
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold/Tri-Metal	Brass, Gold/Tri-Metal
Dielectric Type	PE (HD)	PE (HD)
Body Material & Plating	Brass, Nickel Over Copper	Brass, Tinned Copper
Coupling Nut Material & Plating	Brass, Nickel Over Copper	Brass, Tinned Copper

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA9764 - xx uu

 cm = Centimeters
 <blank> = Inches
 Length


 Example: FMCA9764-12 = 12 inches long cable
 FMCA9764-100cm = 100 cm long cable

10KV Male to 10KV Female Bulkhead Cable RG303HV Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [10KV Male to 10KV Female Bulkhead Cable RG303HV Coax FMCA9764](#)

URL: <https://www.fairviewmicrowave.com/10kv-male-to-10kv-female-bulkhead-cable-rg303hv-coax-fmca9764-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



- NOTES:**
1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

Fairview Microwave[®] an INFINIT [®] brand Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1	
DESCRIPTION: 10KV Male Connector to 10KV Female Bulkhead Mount Connector using RG303HV Coax			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS IN LARGE MILLIMETERS	X = ±.2 [5] .XX = ±.02 [.5] .XXX = ±.005 [.13]	FRACTIONS: ± 1/32 ANGLES ± 1°	CABLE LENGTH TOLERANCES: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.			
SIZE: A	CAGE CODE: 3FKR5	DRAWN BY: LNAGARAJ	ITEM NO.: FMC-A9764
REV	REV	REV	REV