



20KV Male to SHV Plug Cable RG213HV Coax

The 20KV male to SHV plug cable using RG213HV coax, part number FMCA9783, from Fairview Microwave is in-stock and ships same day. This Fairview 20KV to SHV cable assembly has a male to plug gender configuration with 50 ohm RG213HV coax. Our 20kV high voltage RF cable assemblies are designed to handle higher voltages and minimize the risk of electric shock. Both the connectors used in this cable assemblies have recessed contact design to withstand unmated higher voltage. These cable assemblies are commonly used in applications where high voltage transmission and RF signal integrity are critical. These cable assemblies are constructed with high-quality insulation materials capable of withstanding higher voltages, ensuring safety and preventing electrical breakdown. Our cable assemblies are built with durable and flexible materials to withstand harsh environmental conditions and repetitive movements, ensuring reliable performance over extended periods.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	T	ур	Max	U	nits
Velocity of Propagation		6	59			%
Operating Voltage (DC)				20,000	,	Vdc
Test Voltage (DC)				30,000		V

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Weight 0.22 lbs [99.79 g]

Cable

Cable Type RG213HV
Impedance 50 Ohms
Inner Conductor Material and Plating Copper, Bare
Dielectric Type PE
Number of Shields 1

Jacket Material Polyurethane

Jacket Diameter 0.394 in [10.01 mm]

Repeated Minimum Bend Radius 1.969 in [50.01 mm]



Configuration:

- 20KV Male
- SHV Plug
- RG213HV

Features:

- 69% Phase Velocity
- Polyurethane Jacket
- Voltage rating of 10kV
- Recessed Contacts

Applications:

- General Purpose
- Laboratory Use
- High voltage power supplies/Amplifiers
- Nuclear instrumentation
- Test and measurement equipment

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2
Туре	20KV Male Bayonet	SHV Plug Bayonet
Specification	MIL-STD-202	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold/Tri-Metal	Brass, Gold
Contact Plating Spec.		30 µin minimum
Dielectric Type	PE (HD)	PTFE
Body Material & Plating	Brass, Tinned Copper	Brass, Nickel
Body Plating Spec.		100 μin minimum
Coupling Nut Material & Plating	Brass, Tinned Copper	Brass, Nickel
Coupling Nut Plating Spec.		100 µin minimum

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:

Values at 25°C, sea level.

How to Order

Part Number Configuration:



Example: FMCA9783-12 = 12 inches long cable

FMCA9783-100cm = 100 cm long cable

20KV Male to SHV Plug Cable RG213HV Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 20KV Male to SHV Plug Cable RG213HV Coax FMCA9783

URL: https://www.fairviewmicrowave.com/20kv-male-to-shv-plug-cable-rg213hv-coax-fmca9783-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





