



## RA SHV Plug to RA SHV Plug Cable RG400 Coax

The RA SHV plug to RA SHV plug cable using RG400 coax, part number FMCA3165, from Fairview Microwave is in-stock and ships same day. This Fairview SHV to SHV cable assembly has a plug to plug gender configuration with 50 ohm flexible RG400 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3165 SHV plug to SHV plug cable assembly operates to 300 MHz. The right angle SHV interfaces on the RG400 cable allow for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness. Safety high voltage connectors are designed to allow signal transmission with high voltage ratings without safety risk for the operators. Both the pin and socket contacts are securely recessed inside the insulation to guard against potential electrical shock when live unmated connectors are handled.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Min	Ty	/p	Max	Units
DC			300	MHz
	7	0		%
	32 [10	04.99		pF/ft [pF/m]
			1,900	Vrms
		DC 7	DC 70	DC 300 70 32 [104.99]

### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	100	250	300			MHz
Insertion Loss (Typ.)	0.044	0.061	0.066			dB/ft
	0.14	0.2	0.22			dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector.

### **Mechanical Specifications**

### **Cable Assembly**

Length\* 0 in [0 mm]
Weight 0.39 lbs [176.9 g]

## Cable

Cable Type RG400
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Dielectric Type PTFE
Number of Shields 2



## **Configuration:**

- SHV Plug Right Angle
- SHV Plug Right Angle
- RG400

## Features:

- Max Frequency 300 MHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket
- Dielectric withstanding of 5kV
- Shock, Moisture & Corrosion resistant
- Recessed contacts prevent shock hazards

# **Applications:**

- General Purpose
- Laboratory Use
- Nuclear Instrumentation
- High Voltage Electrical Transmission
- Semiconductor Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter Silver Plated Copper Braid Silver Plated Copper Braid

FEP, Tan

0.195 in [4.95 mm]

Repeated Minimum Bend Radius

1 in [25.4 mm]

#### **Connectors**

Description	Connector 1	Connector 2			
Туре	SHV Plug	SHV Plug			
Specification	MIL-STD-348B	MIL-STD-348B			
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Brass, Gold over Nickel ov	er copperBrass, Gold over Nicl			
Dielectric Type	Teflon	Teflon			
Body Material & Plating	Brass, Tinned Cop	per Brass, Tinned Copper			
Coupling Nut Material & Pla	ating Brass, Tinned Cop	oer Brass, Tinned Copper			
Hex Size	7/16 Inch	7/16 Inch			

**Environmental Specifications** 

**Temperature** 

Operating Range

-55 to +165 deg C

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data** 

Notes:

**How to Order** 

Part Number Configuration:

FMCA3165 - xx uu | cm = Centimeters | chlank> = Inches | Length

Example: FMCA3165-12 = 12 inches long cable

FMCA3165-100cm = 100 cm long cable





RA SHV Plug to RA SHV Plug Cable RG400 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA SHV Plug to RA SHV Plug Cable RG400 Coax FMCA3165

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


URL: https://www.fairviewmicrowave.com/ra-shv-plug-to-ra-shv-plug-cable-rg400-coax-fmca3165-p.aspx

	ient improv											
												garding the
suitability	of the par	t describ	ed hereir	n for any	/ particula	ar purpose	, and Fair	view M	crowave	does no	ot assume	any liability
arising ou	t of the use	e of any	part or do	ocument	ation.							

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







RA SHV Plug to RA SHV Plug Cable RG400 Coax

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689