

4.3-10 Female Low PIM Connector Solder Attachment 4 Hole Flange For RG402, RG402 Tinned, .141 SR Cable Cable IP67 Rated

4.3-10 female 4 hole flange mount connector with solder/solder attachment for RG402, RG402 Tinned and .141 SR Cable, part number FMCN1174, from Fairview Microwave is in-stock and ships same day. This 4.3-10 female connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.08:1. The 4.3-10 female connector also has low passive intermodulation (PIM) of -166 dBc. Fairview's FMCN1174 4 hole flange 4.3-10 connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Our FMCN1174 connector has an IP67 rating to protect against dust and temporary moisture protection under immersion conditions.

Fairview's 4.3-10 female 4 hole flange connector FMCN1174 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.08:1	
Insertion Loss			0.13	dB
Passive Intermodulation		-166		dBc
Operating Voltage (AC)			500	Vrms
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size	
Length	1 in [25.4 mm]
Width/Dia.	1 in [25.40 mm]
Height	0.95 in [24.13 mm]
Weight	0.079 lbs [35.83 g]
Mating Cycles	100 Cycles

Material Specifications

Description	Material	Plating
Contact	Brass	Silver
Insulation	PTFE	
Outer Conductor	Brass	Tri-Metal
Body	Brass	Tri-Metal



Configuration:

- 4.3-10 Female Connector
- Straight Body Geometry
- RG402, RG402 Tinned, .141 SR Cable Interface Type
- Solder/Solder Attachment
- 4 Hole Flange
- Low PIM Design

Features:

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.08:1
- PIM levels better than -166 dBc
- Silver Plated Brass Contact
- IP 67 Rated
- Corrosion Resistant Tri-Metal Finish
- Low-PIM rating of -166 dBc
- Low Coupling Torque

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Wireless Communications
- Custom Cable Assemblies
- Low PIM Applications
- Mobile Communications Systems
- Distributed Antenna Systems (DAS)

Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Gasket	Silicone Rubber
--------	-----------------

Environmental Specifications

Temperature

Operating Range -55 to +90 deg C
Ingress Protection (IP) Rating IP 67 Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

4.3-10 Female Low PIM Connector Solder Attachment 4 Hole Flange For RG402, RG402 Tinned, .141 SR Cable Cable IP67 Rated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4.3-10 Female Low PIM Connector Solder Attachment 4 Hole Flange For RG402, RG402 Tinned, .141 SR Cable Cable IP67 Rated FMCN1174](#)

URL: <https://www.fairviewmicrowave.com/4.3-10-female-rg402-rg402-tinned-.141-sr-cable-connector-fmcn1174-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

1. STRIP CABLE AS SHOWN, DO NOT NICK CENTER CONDUCTOR.
2. INSERT CABLE INTO BODY UNTIL OUTER CONDUCTOR BOTTOMS OUT. SOLDER OUTER CONDUCTOR TO BODY.

STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 4.3-10 Female Low PIM Connector Solder Attachment 4 Hole Flange For RG402, RG402 Tinned, .141 SR Cable Cable IP67 Rated		DWG NO FMCN1174	CAGE CODE 3FKR5		
CAD FILE	111716	SHEET	SCALE	N/A	SIZE A 2233