


HN Male Right Angle Connector Clamp/Solder Attachment for RG142, RG223, RG400 Cable



FMCN45902

Configuration

- HN Male Connector
- MIL-STD-348
- 50 Ohms
- Right Angle Body Geometry
- Connector Interface Types: RG142, RG223, RG400

Features

- Silver Plated Contact
- Contact plating according to QQ-S-365

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

FMCN45902 HN male right angle coax connector has an interface type of HN male which is compatible with RG142, RG223, and RG400 cables and has a 50 Ohms impedance. Fairview Microwave's HN male connector uses clamp/solder as an attachment method.

The Fairview Microwave HN male coax connector has a PTFE dielectric type. Fairview Microwave's HN coax connector has a brass body with nickel plating. This threaded RF connector can operate at temperatures ranging from -65 to +165 degrees C. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings above.

This HN male RF connector with coax termination is designed to be used with RG142, RG223, RG400 cables. Our high-quality FMCN45902 connector features a QQ-N-290 body plating specification. This HN connector has a silver inner contact plating.

This Fairview Microwave male HN connector will ship the same business day as purchased. Our HN male connector is part of over 40,000 RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width	0.9 in [22.86 mm]
Height	1.47 in [37.34 mm]
Weight	0.161 lbs [73.03 g]

HN Male Right Angle Connector Clamp/Solder Attachment for RG142, RG223, RG400 Cable



FMCN45902

Material Specifications

Description	Material	Plating
Contact		Silver QQ-S-365
Insulation	PTFE	
Body	Brass	Nickel QQ-N-290
Coupling Nut	Brass	Nickel QQ-N-290

Environmental Specifications

Temperature Operating Range	-65 to +165 deg C
---------------------------------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

HN Male Right Angle Connector Clamp/Solder Attachment for RG142, RG223, RG400 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [HN Male Right Angle Connector Clamp/Solder Attachment for RG142, RG223, RG400 Cable FMCN45902](#)

URL: <https://www.fairviewmicrowave.com/hn-male-rg142-rg223-rg400-connector-fmcn45902-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN45902 CAD Drawing

HN Male Right Angle Connector Clamp/Solder Attachment for RG142, RG223, RG400 Cable

