

FMCN45933 DATA SHEET

2.4mm Female (Jack) PCB Surface Mount with Round Contact 50GHz VSWR1.25

FMCN45933 2.4mm female PCB RF connector has a 50 Ohms impedance. Our 2.4mm female PCB connector operates at a maximum frequency of 50 GHz. Our high-quality radio frequency co-axial coaxial connector is used for general purpose test and printed circuit board applications. This 2.4mm female RF connector is stocked to be readily available for same business day shipment.

The Fairview Microwave 2.4mm female PCB connector has a VSWR of 1.25:1. This 2.4mm PCB connector has a brass body with gold plating. Our FMCN4533 connector uses a beryllium copper contact. This RF connector can operate at temperatures ranging from -40 to +165 degrees C. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings.

Fairview Microwave RF connector block has a maximum inner conductor and outer conductor resistance of 4 mOhms and 2.5 mOhms respectively. Our 2.4mm female RF connector with PCB termination has a 0.353 dB maximum insertion loss. The radio frequency connector is made from brass along with a contact life of 500 cycles or more. This 2.4mm connector has a beryllium copper inner contact plating. Fairview Microwave's 2.4mm jack connector has a maximum operating voltage of 150 Vrms and a dielectric withstanding voltage of 500 Vrms.

This Fairview Microwave 2.4mm female connector will ship the same business day as purchased. Our 2.4mm female connector is part of the RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		50	GHz
VSWR			1.25:1	
Insertion Loss			0.353	dB
Operating Voltage (AC)			150	Vrms
DWV (AC)			500	Vrms
Inner Cond. DC Resistance	e		4	mOhms
Outer Cond. DC Resistance	e		2.5	mOhms
Insulation Resistance	5,000			MOhms
RF Leakage	100			dB

Mechanical Specifications

Size

Length 0.46 in [11.68 mm]
Width/Dia. 0.25 in [6.35 mm]
Height 0.25 in [6.35 mm]
Weight 0.02 lbs [9.07 g]
Mating Cycles 500 Cycles
Mating Torque 9.74 to 15 in-lbs [1.10 to 1.70 Nm]

Cable Retention Force 4.5 lbs [2.04 kg]

Configuration:

- 2.4mm Female Connector
- 50 Ohms
- Straight Body Geometry
- Solder Attachment

Features:

- Operating Frequency of 50 GHz Max.
- Excellent VSWR of 1.25:1
- Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- PCB Applications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Material	Plating	
Contact	Beryllium Copper	Nickel	
Insulation	PEI		
Outer Conductor	Brass	Nickel	
Body	Brass	Nickel	

Environmental Specifications

Temperature

Operating Range Humidity Thermal Shock Salt Spray -40 to +165 deg C

MIL-STD-202, Method 106

MIL-STD-202, Method 107, Condition B MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

2.4mm Female (Jack) PCB Surface Mount with Round Contact 50GHz VSWR1.25 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.4mm Female (Jack) PCB Surface Mount with Round Contact 50GHz VSWR1.25 FMCN45933

URL: https://www.fairviewmicrowave.com/2.4mm-female-pcb-connector-fmcn45933-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1 Page 2 of 3





