



FMCA9971

Configuration

Connector 1: 2.4mm Male
Connector 2: 2.4mm Male
Cable Type: FM-P047
Coax Flex Type: Flexible

Features

- · Max Frequency 50 GHz
- · Shielding Effectivity > 90 dB
- · 70% Phase Velocity
- · Double Shielded
- FEP Jacket

Applications

· General Purpose

· Laboratory Use

Description

The 2.4mm male to 2.4mm male cable using FM-P047 coax, part number FMCA9971, from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-P047 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA9971 2.4mm male to 2.4mm male cable assembly operates to 50 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|------------|---------|--------------|
| Frequency Range | DC | | 50 | GHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | | 70 | | % |
| RF Shielding | 90 | | | dB |
| Capacitance | | 29 [95.14] | | pF/ft [pF/m] |

Specifications by Frequency





FMCA9971

| Part Number | Length | Description | F1 | F2 | F3 | F4 | F5 | Units | Weight (lbs) |
|-------------|----------------|-----------------------|------|------|-------|-------|-------|-------|--------------|
| | | Frequency | 2500 | 5000 | 10000 | 20000 | 50000 | MHz | |
| FMCA9971 | Custom Lengths | Insertion Loss (Typ.) | 0.31 | 0.46 | 0.675 | 1.005 | 1.548 | dB/ft | |
| FIVICA9971 | Available | | 1.03 | 1.5 | 2.22 | 3.3 | 5.08 | dB/m | |
| FMCA9971-6 | 6 inch | Insertion Loss (Typ.) | 0.29 | 0.41 | 0.6 | 0.87 | 1.34 | dB | 0.017 |
| FMCA9971-12 | 12 inch | Insertion Loss (Typ.) | 0.44 | 0.64 | 0.93 | 1.37 | 2.12 | dB | 0.018 |
| FMCA9971-24 | 24 inch | Insertion Loss (Typ.) | 0.76 | 1.1 | 1.61 | 2.37 | 3.67 | dB | 0.022 |
| FMCA9971-36 | 36 inch | Insertion Loss (Typ.) | 1.07 | 1.55 | 2.28 | 3.38 | 5.21 | dB | 0.026 |
| FMCA9971-48 | 48 inch | Insertion Loss (Typ.) | 1.38 | 2.01 | 2.96 | 4.38 | 6.76 | dB | 0.03 |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.04 x sqrt(fGHz) dB
Loss due to Connector 2: 0.04 x sqrt(fGHz) dB
Base Weight: 0.018 pounds
Additional Weight per Inch: 0.00031 pounds

Mechanical Specifications

Cable Assembly

Weight 0.018 lbs [8.16 g]

Cable

Cable Type FM-P047
Impedance 50 Ohms
Inner Conductor Type Solid

Inner Conductor Material and Plating Copper, Silver Dielectric Type FEP

Number of Shields2Shield Layer 1Silver Plated Copper TapeShield Layer 2Silver Plated Copper Braid

Jacket MaterialFEP, BlueJacket Diameter0.056 in [1.42 mm]

One Time Minimum Bend Radius

O.2 in [5.08 mm]

Repeated Minimum Bend Radius

O.4 in [10.16 mm]





FMCA9971

Connectors

| Description | Connector 1 | Connector 2 | | |
|------------------------------------|------------------------------------|------------------------------------|--|--|
| Туре | 2.4mm Male | 2.4mm Male | | |
| Impedance | 50 Ohms | 50 Ohms | | |
| Configuration | Straight | Straight | | |
| Contact Material and Plating | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nicke | | |
| Contact Plating Specification | 50 μin minimum | 50 μin minimum | | |
| Dielectric Type | PEI | PEI | | |
| Body Material and Plating | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel | | |
| Body Plating Specification | 50 μin minimum | 50 µin minimum | | |
| Coupling Nut Material and Plating | Passivated Stainless Steel | Passivated Stainless Steel | | |
| Coupling Nut Plating Specification | ASTM-A582 | ASTM-A582 | | |
| Hex Size | 5/16 inch | 5/16 inch | | |
| Torque | 8 in-lbs 0.9 Nm | 8 in-lbs 0.9 Nm | | |
| Seal Gasket Material | Silicone Rubber Silicone Rubber | | | |

Environmental Specifications

Operating Range Temperature

-65 to +150 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:






FMCA9971

Typical Performance Data

How to Order



Example: FMCA9971-12 = 12 inches long cable

FMCA9971-100cm = 100 cm long cable

2.4mm Male to 2.4mm Male Cable FM-P047 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/ microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: 2.4mm Male to 2.4mm Male Cable FM-P047 Coax FMCA9971

URL: https://www.fairviewmicrowave.com/2.4mm-male-to-2.4mm-male-cable-fm-p047-coax-fmca9971-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

