	6	5 4	3 2 1
			ZONE REV. DESCRIPTION DATE CHANGED BY APPROVED BY A INITIAL RELEASE 09/07/2023 BPUCHASKI GUTTADAURO
F	WIRING TABLE		
	DB15 F TERMINAL BLOCK #		
	1 1 2 2		
E	3 3 4 4		Image: Constraint of the second state of the seco
	5 5 6 6 7 7	= = = = = = = = = = = = = = = = = = =	
_	8 8 9 9	DB15 FEMALE	
	10 10 11 11	D-SUB CONNECTOR	
D	12 12 13 13	-	
	14 14 15 15	-	/2X, 8 POSITION / TERMINAL BLOCK
	GROUND 16	20°/	
с	4X R.		$\begin{array}{c ccccccccccccccccccccccccccccccccccc$
	2X R	06[1.5] - 1.312 - [33.3] - [33.3]	[5.0] [0.8]
в		RECOMMENDED PANEL OPENING (MAX PANEL THICKNESS: 0.06")	
	NOTES:		
	VOLTAGE RATING: 1000V AC CURRENT RATING: 3 AMPS	AND 500V DC.	TOLERANCES: X = ±.2 [5] FRACTIONS .XX = ±.02 [0.5] ± 1/32
A	REGULATORY COMPLIANCE: EU RoHS DIRECTIVE (MOST RECENT RELATED VERSION)		.XXX = ±.005 [0.13] ANGLES ± 1° Website: www.FairviewMicrowave.com SCALE SHEET CABLE LENGTH TOLERANCES: \$12 [305] < 60 [1524] = +2 [51] / -0
OR SO	R WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE I OFTWARE WERE EXPORTED FROM THE UNITED STATES IN A	PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART LECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR CCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION	ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION A 25//DE DDLICLIA SIZE
	DNTRARY TO U.S. LAW PROHIBITED. DS Rev-D4 Asize 6	5 4	COLORS MAY VARY A SFKRS DFUCHASKI FIVICIN45977 A 3 2 1