

TNC Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.0394 inches diameter, 18GHz VSWR1.2



FMCN46002

Configuration

- · TNC Female Connector
- 50 Ohms

Features

- · Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.2:1

• 45 Degree Body Geometry

PCB

Applications

· General Purpose Test

Copper-Tin-Zinc Alloy Plated Beryllium Copper Contact

Description

45° Angle TNC Female PCB Mount Connector, part number FMCN46002, from Fairview Microwave is in-stock and shipssame day. This TNC female connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.2:1.

Fairview's 45° Angle TNC female PCB connector FMCN46002 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.2:1	
Insertion Loss			0.42	dB
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Inner Conductor DC Resistance			1.5	mOhms
Outer Conductor DC Resistance			1	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Mechanical Specifications

Size

Length Width Height Weight Mating Cycles 0.898 in [22.81 mm] 0.433 in [11.00 mm] 1.21 in [30.73 mm] 0.015 lbs [6.8 g] 500 Cycles



TNC Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.0394 inches diameter, 18GHz VSWR1.2



FMCN46002

Material Specifications

Description	Material	Plating	
Contact	Beryllium Copper	Copper-Tin-Zinc Alloy	
Insulation	Teflon		
Body	Brass	Gold over Nickel over Copper	

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Humidity MIL-STD-202, Method 106

Thermal Shock MIL-STD-202, Method 107, Condition B Salt Spray MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

TNC Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.0394 inches diameter, 18GHz VSWR1.2 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: TNC Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.0394 inches diameter, 18GHz VSWR1.2 FMCN46002

URL: https://www.fairviewmicrowave.com/tnc-female-connector-fmcn46002-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN46002 CAD Drawing

TNC Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.0394 inches diameter, 18GHz VSWR1.2

