

N Male (Plug) Connector Clamp/Solder Attachment  
for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR Cable



**FMCN5265**

**Configuration**

- N Male Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR, LMR-LW400, TCOM-400, TCOM-400-FR

**Features**

- Operating Frequency of 8 GHz Max.
- Gold Plated Brass Contact
- Contact plating according to ASTM-B488

**Applications**

- General Purpose Test
- Custom Cable Assemblies

**Description**

Type N Male Standard Connector Clamp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR, LMR-LW400, TCOM-400 and TCOM-400-FR Cable, part number FMCN5265, from Fairview Microwave is in-stock and ships same day. This type N male connector operates up to a maximum frequency of 8 GHz.

Fairview's type N male connector FMCN5265 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
VSWR		1.15:1		
Operating Voltage (AC)			1,000	Vrms
Dielectric Withstanding Voltage (AC)			2,500	Vrms
Impedance		50		Ohms

**Mechanical Specifications**

**Size**

- Length 1.5 in [38.1 mm]
- Width 0.8 in [20.32 mm]
- Height 0.8 in [20.32 mm]
- Weight 0.112 lbs [50.8 g]

N Male (Plug) Connector Clamp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR Cable



**FMCN5265**

**Material Specifications**

Description	Material	Plating
Contact	Brass	Gold ASTM-B488
Insulation	PTFE	
Body	Brass	Nickel ASTM-B689
Coupling Nut	Brass	Nickel ASTM-B689

**Environmental Specifications**

<b>Temperature</b> Operating Range	-65 to +165 deg C
---------------------------------------	-------------------

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

N Male (Plug) Connector Clamp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Male \(Plug\) Connector Clamp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR Cable FMCN5265](#)

URL: <https://www.fairviewmicrowave.com/n-male-lmr-400-lmr-400-db-lmr-400-fr-lmr-400-llpx-lmr-400-uf-lmr-400-uf-fr-lmr-lw400-tcom-400-tcom-400-fr-connector-fmcn5265-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMCN5265 CAD Drawing

N Male (Plug) Connector Clamp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-FR, LMR-400-LLPX, LMR-400-UF, LMR-400-UF-FR Cable

