

FMCN1261 DATA SHEET

SSMC Jack PCB Connector Thru Hole Solder Attachment

SSMC jack connector with solder attachment for thru hole PCB, part number FMCN1261, from Fairview Microwave is in-stock and ships same day. This SSMC jack connector operates up to a maximum frequency of 12.4 GHz.

Fairview's SSMC jack connector FMCN1261 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		12.4	GHz
Insertion Loss			0.3	dB
Operating Voltage (AC)			250	Vrms
High Potential Voltage 5 MHz			400	Vrms
Inner Cond. DC Resistance	e		4	mOhms
Outer Cond. DC Resistance	е		1	mOhms
Insulation Resistance	1,000			MOhms
RF Leakage	-50			dB

Mechanical Specifications

Size

Length Width/Dia. Weight

Mating Cycles Mating Torque 0.419 in [10.64 mm] 0.156 in [3.96 mm]

0.0055 lbs [2.49 g]

500 Cycles

1.75 to 2 in-lbs [0.20 to 0.23 Nm]

Material Specifications

Description	Material	Plating	
Contact	Beryllium Copper	Gold MIL-G-45204	
Insulation	Teflon		
Outer Conductor	Beryllium Copper	Gold MIL-G-45204	
Body	Brass	Gold MIL-G-45204	



Configuration:

- SSMC Jack Connector
- · Straight Body Geometry
- Thru Hole Interface Type
- Solder Attachment

Features:

- Operating Frequency of 12.4 GHz Max.
- Gold Plated Beryllium Copper Contact
- Contact plating according to MIL-G-45204
- Small SSMC connector form factor (50% smaller than SMA, radially)
- · Reliable threaded coupling
- IEC 60169-20 SSMC connector interface
- · In stock and ready to ship

Applications:

- General Purpose Test
- Space Saving for PCB Applications
- Software defined radio (SDR)
- Avionics
- A/D Modules
- · Ultra Wideband Digital Receivers
- Data Acquisition
- RADAR/SONAR

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature

Operating Range Shock Vibration Salt Spray -65 to +165 deg C Method 213, Condition B, 75G @6ms @1/2 sine

Method 204, Condition D (20G)

Method 101, Condition B, 5% salt solution

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

SSMC Jack PCB Connector Thru Hole Solder Attachment from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SSMC Jack PCB Connector Thru Hole Solder Attachment FMCN1261

URL: https://www.fairviewmicrowave.com/ssmc-jack-thru-hole-pcb-connector-fmcn1261-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





