



# MCX Plug Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable

MCX plug connector with solder attachment for RG405, RG405 Tinned and .086 SR, part number FMCN1281, from Fairview Microwave is in-stock and ships same day. This MCX plug connector operates up to a maximum frequency of 6 GHz and offers good VSWR of 1.37:1.

Fairview's MCX plug connector FMCN1281 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

# **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.37:1	
Operating Voltage (AC)			335	Vrms
DWV (AC)			1,000	Vrms
High Potential Voltage at 4 and 7 MHz			670	Vrms
Corona Discharge at 70,000 feet			250	Vrms
Insulation Resistance	10,000			MOhms

## **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 1					GHz
Insertion Loss, Max	0.1					dB

Electrical Specification Notes: RF leakage: 55 dB at 2.5 GHz.

## **Mechanical Specifications**

Size

 Length
 0.445 in [11.3 mm]

 Width/Dia.
 0.196 in [4.98 mm]

 Weight
 0.01 lbs [4.54 g]

 Mating Cycles
 500 Cycles

#### **Material Specifications**

Description	Material	Plating			
Contact	Brass	Gold over Nickel 30 µin minimum			



# **Configuration:**

- MCX Plug Connector
- MIL-C-39012
- 50 Ohms
- Straight Body Geometry
- RG405, RG405 Tinned, .086 SR Interface Type
- Solder Attachment

#### Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.37:1
- Gold over Nickel Plated Brass Contact
- 30 µin minimum contact plating

# **Applications:**

- General Purpose Test
- · Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Insulation	PTFE	
Body	Brass	Gold over Nickel 10 µin minimum

### **Environmental Specifications**

Temperature

Operating Range -65 to +165 deg C Humidity MIL-STD-202, Method 106

Shock MIL-STD-202, Method 213, Condition B
Vibration MIL-STD-202, Method 204, Condition B
Thermal Shock MIL-STD-202, Method 107, Condition F
Salt Spray MIL-STD-202, Method 101, Condition B

**Compliance Certifications** (see product page for current document)


#### **Plotted and Other Data**

Notes:






#### **Assembly Instruction**



PLACE CONTACT OVER CENTER CONDUCTOR AS SHOWN.
 SOLDER CONTACT TO CENTER CONDUCTOR AS SHOWN.



3. INSERT BODY INTO THE CONTACT UNTIL CONTACT SITS FLUSH TO THE DIELECTRIC. SOLDER BODY TO CABLE.





MCX Plug Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: MCX Plug Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable FMCN1281

URL: https://www.fairviewmicrowave.com/mcx-plug-rg405-rg405-tinned-.086-sr-connector-fmcn1281-p.aspx









#### STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].				TIME.	
MCX Plug Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable	DWG NO FMCN1281			CAGE CODE 3FKR5		
	CAD FILE 011818	SHEET 1 OF 2	SCAL	E N/A	SIZE A	7361