

FMCN1432 DATA SHEET

4.3-10 Female Connector Solder Attachment For SPP-250-LLPL Cable Low PIM

4.3-10 female connector with solder/solder attachment for SPP-250-LLPL, part number FMCN1432, from Fairview Microwave is in-stock and ships same day. This 4.3-10 female connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.25:1. The 4.3-10 female connector also has low passive intermodulation (PIM) of -165 dBc.

Fairview's 4.3-10 female connector FMCN1432 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units	
Frequency Range	DC		6	GHz	
VSWR			1.25:1		
Insertion Loss			0.1	dB	
Passive Intermodulation			-165	dBc	
Operating Voltage (AC)			250	Vrms	
Insulation Resistance	5,000			MOhms	

Electrical Specification Notes: Insertion Loss is 0.04*sqrt(FGHz)

Mechanical Specifications

Weight

0.085 lbs [38.56 g]

Material Specifications

Material	Plating
Phosphor Bronze	Silver
PTFE	
Phosphor Bronze	Tri-Metal
Brass	Tri-Metal
	Phosphor Bronze PTFE Phosphor Bronze

Environmental Specifications

Temperature

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- 4.3-10 Female Connector
- 50 Ohms
- Straight Body Geometry
- SPP-250-LLPL Interface Type
- Solder/Solder Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.25:1
- PIM levels better than -165 dBc
- Silver Plated Phosphor Bronze Contact

Applications:

- General Purpose Test
- Custom Cable Assemblies
- Low PIM Interconnects
- Distributed Antenna Systems (DAS)
- Low PIM Jumpers
- Low PIM Jumper
 Low PIM Testing
- Low PIM Connections


301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

Fairview Microwave







Assembly Instruction




1. STRIP CABLE AS SHOWN, CHAMFER CENTER CONDUCTOR AND DEBURR CABLE.



2. SLIDE INSULATOR ③ OVER CABLE CENTER CONDUCTOR. INSERT CENTER CONTACT AND SOLDER. WRAP THE CABLE BY SOLDER WIRE.



3. PUSH THE CONNECTOR BODY INTO THE CABLE, UNTIL IT STOPS. SOLDER THE CONNECTOR BODY WITH CABLE AND COVER HEATSHRINK SLEEVE.



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






4.3-10 Female Connector Solder Attachment For SPP-250-LLPL Cable Low PIM from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 4.3-10 Female Connector Solder Attachment For SPP-250-LLPL Cable Low PIM FMCN1432


URL: https://www.fairviewmicrowave.com/4.3-10-female-spp-250-llpl-connector-fmcn1432-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







STANDARD TOLERANCES .X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
4.3-10 Female Connector Solder Attachment For SPP-	dwg no D3F11A-A44W01			CAGE CODE 3FKR5		
250-LLPL Cable Low PIM	CAD FILE 12/14/17	SHEET	SCAI	E N/A	SIZE A	CN2245

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689