

## N Directional Coupler 30 dB from 100 MHz to 800 MHz Rated to 500 Watts

Directional couplers are indispensable components for isolating, separating and combining signals. For example, they provide a simple way of sampling microwave signals. They also can make accurate attenuator measurements since reflections are eliminated. The FMCP1143-30 is a 30 dB directional coupler that operates from 100 to 800 MHz and can handle up to 500 Watts (CW) with 20 dB directivity minimum and 1.2:1 VSWR maximum. The package interface uses N female connectors.

The FMCP1143-30 is part of Fairview Microwave's family of directional/dual-directional couplers that offer coupling ratios up to 50 dB with excellent performance featuring high directivity, low insertion loss and VSWR. They are available in both narrow and broad bandwidths and can be used in a wide variety of applications including signal sampling, VSWR measurements, power combining and distribution.



### Features:

- Directional Coupler
- N Female Connectorized Design
- 100 to 800 MHz Frequency Range
- Coupling 30±1.5 dB
- Directivity > 20 dB
- VSWR < 1.2:1
- Max Power 500 Watts (CW)

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	100		800	MHz
Impedance		50		Ohms
Coupling	29	30	33	dB
Freq. Sensitivity		±0.7	±1.5	dB
Insertion Loss		0.2	0.4	dB
Directivity	20	22		dB
Main Line VSWR		1.15:1	1.2:1	
Sec. Line VSWR		1.15:1	1.2:1	
Input Power (CW)			500	Watts
Input Power (Peak) 10% Duty Cycle, 10us PW			3	kWatts

### Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

### Mechanical Specifications

<b>Size</b>	
Length	12.402 in [315.01 mm]
Width/Dia.	1.521 in [38.63 mm]
Height	1.053 in [26.75 mm]
Weight	2.14 lbs [970.69 g]
Housing Material and Plating	Aluminum

#### Configuration

Input Connector	N Female
Output Connector	N Female
Coupled Connectors	N Female

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C
Humidity	100% RH at 35°C, 95%RH at 40°C

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Shock 20G for 11msec half sine wave, 3 axis both directions  
Vibration 25g RMS (15 degrees 2KHz) endurance, 1 hour per axis  
Altitude 30,000 ft.

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

N Directional Coupler 30 dB from 100 MHz to 800 MHz Rated to 500 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Directional Coupler 30 dB from 100 MHz to 800 MHz Rated to 500 Watts FMCP1143-30](#)

URL: <https://www.fairviewmicrowave.com/directional-standard-30-db-100-mhz-to-800-mhz-fmcp1143-30-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

