

FMCR1028 DATA SHEET

Circulator 2.92mm Female with 13 dB Isolation from 22 GHz to 33 GHz Rated to 10 Watts

The FMCR1028 is an RF circulator offering a forward and reverse power rating of 10 watts over an operational frequency band of 22 to 33 GHz. This coaxial part uses 2.92mm female connectors on all ports and has a minimum of 13 dB of isolation.

Fairview Microwave offers a wide variety of circulators to fit your needs. These unique devices enable two signals to use one channel. The classic use of this three port device is for the line/coax between an antenna and a transceiver, allowing the receive signal to come from the antenna (port 1) to the receiver (port 2) while the transmit signal goes from the transmitter (port 3) to the antenna (port 1). An circulator can be created by terminating one port into a matched load. These components can be used in antenna transmitting and receiving, radar, amplifier systems and anything that requires isolation from a signal reflection and the ability to send signals in opposite directions down a single channel. These circulators feature excellent insertion loss, high isolation and reliability.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	22		33	GHz
Impedance		50		Ohms
Insertion Loss			1.7	dB
Isolation	13			dB
VSWR			1.7:1	
Forward Power, CW			10	Watts

Features:

- Forward/Reverse Power 10 watts
- Wide-Band Operating Frequency Range of 22 to 33 GHz
- Female 2.92mm Connectors
- Low VSWR of 1.70:1 Max
- Low Insertion Loss of 1.7 dB
- Good Isolation Performance of 13 dB Minimum

Applications:

- Radar Systems
- Military
- Wireless Radio Systems
- Telecom Infrastructure
- Communication Systems
- R&D Labs
- Microwave Radio Systems

Mechanical Specifications

Humidity

Vibration

Altitude

Shock

Size Length Width Height Weight Body Material and Platin	0.98 in [24.89 mm] 0.91 in [23.11 mm] 0.66 in [16.76 mm] 0.066 lbs [29.94 g] ng Copper, Nickel
Configuration Design Direction Connector 1 Connector 2 Connector 3	Single Junction Clockwise 2.92mm Female 2.92mm Female 2.92mm Female
Environmental Specific Temperature Operating Range Storage Range	cations -40 to +85 deg C -40 to +85 deg C

100% RH at 35c 20G for 11msec 25g RMS 30,000 ft. (Epoxy Sealed Controlled environment) Fairview Microwave 301 Leora Ln., Suite 100, Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.


Typical Performance Data



Fairview Microwave



an INFINIT[®] brand



Circulator 2.92mm Female with 13 dB Isolation from 22 GHz to 33 GHz Rated to 10 Watts from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Circulator 2.92mm Female with 13 dB Isolation from 22 GHz to 33 GHz Rated to 10 Watts FMCR1028


URL: https://www.fairviewmicrowave.com/circulator-2.92mm-female-13db-isolation-33-ghz-10-watts-fmcr1028-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT[®] brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689