

2 Way Power Divider 2.92mm Interface from 18 GHz to 40 GHz Rated at 20 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The FMDV1064 is a 2-way high power Wilkinson power divider that operates from 18 to 40 GHz and can handle up to 20 Watts (CW) with 1.2 dB max insertion loss and 16 dB min isolation. The package interface uses 2.92mm female connectors and is REACH and RoHS compliant.

Electrical Specifications

Design Number of Output Ports			Wilkinson 2	
Description	Min	Тур	Мах	Units
Frequency Range	18		40	GHz
Impedance		50		Ohms
Input VSWR		1.4:1	1.5:1	
Output VSWR		1.4:1	1.5:1	
Insertion Loss		0.7	1.2	dB
Isolation	16			dB
Amplitude Balance		±0.2	±0.4	dB
Phase Balance		±3	±4	Degrees
Input Power (CW)			20	Watts
Reverse Power (CW)			0.5	Watts
Input Power (Peak)			200	Watts



FMDV1064 DATA SHEET

Features:

- 2-Way Power Divider
- High Power Wilkinson Design
- 18 to 40 GHz Frequency Range
- Max Power 20 Watts (CW)
- Insertion Loss < 1.2 dB
- Isolation > 16 dB

Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Mechanical Specifications

Size Length Width Height Weight Housing Material and Plating	0.75 in [19.05 mm] 1.02 in [25.91 mm] 0.39 in [9.91 mm] 0.0546 lbs [24.77 g] Aluminum, Gold
Configuration	Connectorized

Package Type Input Connector **Output Connectors**

Environmental Specifications

Temperature **Operating Range**

Storage Range

a]

Connectorized 2.92mm Female 2.92mm Female

-45 to +85 deg C -55 to +125 deg C Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Humidity	100% RH at 35°C, 95% RH at 40°C
Shock	20G for 11msec half sine wave, 3 axis both directions
Vibration	25g RMS (15 degrees 2KHz) endurance, 1 hour per axis
Altitude	30.000 ft. (Epoxy Sealed Controlled environment)
Altitude	30,000 ft. (Epoxy Sealed Controlled environment)


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:




Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







2 Way Power Divider 2.92mm Interface from 18 GHz to 40 GHz Rated at 20 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2 Way Power Divider 2.92mm Interface from 18 GHz to 40 GHz Rated at 20 Watts FMDV1064


URL: https://www.fairviewmicrowave.com/2-way-power-divider-2.92mm-40-ghz-fmdv1064-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689